

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259002

Luminaire Tested: P3AS02R559050DE010 E3DLP1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1259002  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R559050DE010 E3DLP1WH  
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 290.0 lumens  
Efficiency: N/A  
Efficacy: 80.6 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1259002  
CATALOG NUMBER: P3AS02R559050DE010 E3DLP1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1259002  
 CATALOG NUMBER: P3AS02R559050DE010 E3DLP1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 | 101 | 99  | 98  | 97  | 96  | 95  | 93  |    |    |   |
| 2   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 94  | 98  | 95  | 92  | 95  | 92  | 90  | 92  | 90  | 88  | 87  |    |    |   |
| 3   | 102 | 96  | 91  | 87  | 100 | 94  | 90  | 86  | 92  | 88  | 85  | 89  | 86  | 83  | 87  | 85  | 82  | 81  |    |    |   |
| 4   | 97  | 90  | 84  | 80  | 95  | 89  | 83  | 79  | 86  | 82  | 78  | 84  | 81  | 78  | 82  | 79  | 77  | 75  |    |    |   |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 78  | 74  | 81  | 77  | 73  | 80  | 76  | 72  | 78  | 75  | 72  | 70  |    |    |   |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 73  | 68  | 77  | 72  | 68  | 75  | 71  | 68  | 74  | 70  | 67  | 66  |    |    |   |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  | 71  | 67  | 63  | 70  | 66  | 63  | 62  |    |    |   |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 63  | 60  | 67  | 63  | 60  | 67  | 62  | 59  | 58  |    |    |   |
| 9   | 76  | 66  | 61  | 57  | 75  | 66  | 60  | 56  | 65  | 60  | 56  | 64  | 59  | 56  | 63  | 59  | 56  | 55  |    |    |   |
| 10  | 73  | 63  | 57  | 53  | 72  | 62  | 57  | 53  | 62  | 57  | 53  | 61  | 56  | 53  | 60  | 56  | 53  | 52  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 79643 |
| 5°  | 78824 |
| 10° | 76129 |
| 15° | 70352 |
| 20° | 60719 |
| 25° | 47954 |
| 30° | 34031 |
| 35° | 21924 |
| 40° | 13168 |
| 45° | 7412  |
| 50° | 3991  |
| 55° | 1415  |
| 60° | 1272  |
| 65° | 1245  |
| 70° | 1218  |
| 75° | 1101  |
| 80° | 1010  |
| 85° | 755   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7412 cd/sqm



TEST NUMBER: P1259002  
 CATALOG NUMBER: P3AS02R559050DE010 E3DLP1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 33.7   | 11.6      |
| 10°-20°   | 85.7   | 29.6      |
| 20°-30°   | 89.8   | 31.0      |
| 30°-40°   | 52.4   | 18.1      |
| 40°-50°   | 19.6   | 6.8       |
| 50°-60°   | 4.6    | 1.6       |
| 60°-70°   | 2.4    | 0.8       |
| 70°-80°   | 1.4    | 0.5       |
| 80°-90°   | 0.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 209.2  | 72.1      |
| 0°-40°    | 261.6  | 90.2      |
| 0°-60°    | 285.8  | 98.6      |
| 0°-90°    | 290.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 290.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 363 |      |
| 5°  | 358 | 34   |
| 15° | 310 | 86   |
| 25° | 198 | 90   |
| 35° | 82  | 52   |
| 45° | 24  | 20   |
| 55° | 4   | 5    |
| 65° | 2   | 2    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P1259002  
CATALOG NUMBER: P3AS02R559050DE010 E3DLP1WH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 363.2 |
| 2.5°  | 362.1 |
| 5°    | 358.1 |
| 7.5°  | 351.7 |
| 10°   | 341.9 |
| 12.5° | 328.0 |
| 15°   | 309.9 |
| 17.5° | 287.1 |
| 20°   | 260.2 |
| 22.5° | 230.1 |
| 25°   | 198.2 |
| 27.5° | 165.5 |
| 30°   | 134.4 |
| 32.5° | 106.2 |
| 35°   | 81.9  |
| 37.5° | 62.3  |
| 40°   | 46.0  |
| 42.5° | 33.0  |
| 45°   | 23.9  |
| 47.5° | 17.3  |
| 50°   | 11.7  |
| 52.5° | 6.7   |
| 55°   | 3.7   |
| 57.5° | 3.2   |
| 60°   | 2.9   |
| 62.5° | 2.7   |
| 65°   | 2.4   |
| 67.5° | 2.1   |
| 70°   | 1.9   |
| 72.5° | 1.6   |
| 75°   | 1.3   |
| 77.5° | 1.1   |
| 80°   | 0.8   |
| 82.5° | 0.5   |
| 85°   | 0.3   |
| 87.5° | 0.3   |
| 90°   | 0.0   |

(END OF REPORT)