

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259015

Luminaire Tested: P3AS02R609050DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259015
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609050DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 137.0 lumens
Efficiency: N/A
Efficacy: 38.1 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259015

CATALOG NUMBER: P3AS02R609050DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1259015

CATALOG NUMBER: P3AS02R609050DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		67
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32344
5°	32049
10°	31106
15°	29149
20°	25786
25°	21582
30°	16914
35°	12260
40°	8158
45°	5086
50°	2763
55°	803
60°	746
65°	675
70°	641
75°	678
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5086 cd/sqm

TEST NUMBER: P1259015

CATALOG NUMBER: P3AS02R609050DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.7	10.0
10°-20°	35.6	26.0
20°-30°	40.6	29.6
30°-40°	28.8	21.0
40°-50°	13.1	9.5
50°-60°	2.8	2.0
60°-70°	1.3	1.0
70°-80°	0.8	0.6
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	89.9	65.6
0°-40°	118.7	86.6
0°-60°	134.5	98.2
0°-90°	137.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	137.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	148	
5°	146	14
15°	128	36
25°	89	41
35°	46	29
45°	16	13
55°	2	3
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1259015

CATALOG NUMBER: P3AS02R609050DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	147.5
2.5°	147.0
5°	145.6
7.5°	143.1
10°	139.7
12.5°	134.9
15°	128.4
17.5°	120.2
20°	110.5
22.5°	100.1
25°	89.2
27.5°	78.0
30°	66.8
32.5°	56.1
35°	45.8
37.5°	36.7
40°	28.5
42.5°	21.6
45°	16.4
47.5°	12.2
50°	8.1
52.5°	3.8
55°	2.1
57.5°	1.8
60°	1.7
62.5°	1.6
65°	1.3
67.5°	1.2
70°	1.0
72.5°	0.9
75°	0.8
77.5°	0.7
80°	0.5
82.5°	0.4
85°	0.3
87.5°	0.1
90°	0.0

(END OF REPORT)