

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259723

Luminaire Tested: P3AS09R559050DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259723
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559050DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 871.0 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259723

CATALOG NUMBER: P3AS09R559050DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1259723

CATALOG NUMBER: P3AS09R559050DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	239169
5°	236737
10°	228631
15°	211329
20°	182366
25°	144033
30°	102168
35°	65879
40°	39560
45°	22297
50°	12008
55°	4282
60°	3859
65°	3736
70°	3590
75°	3389
80°	3031
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22297 cd/sqm

TEST NUMBER: P1259723

CATALOG NUMBER: P3AS09R559050DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.1	11.6
10°-20°	257.4	29.6
20°-30°	269.8	31.0
30°-40°	157.4	18.1
40°-50°	58.9	6.8
50°-60°	13.9	1.6
60°-70°	7.1	0.8
70°-80°	4.2	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	628.3	72.1
0°-40°	785.7	90.2
0°-60°	858.5	98.6
0°-90°	871.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	871.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1091	
5°	1076	101
15°	931	257
25°	595	270
35°	246	157
45°	72	59
55°	11	14
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1259723

CATALOG NUMBER: P3AS09R559050DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1090.7
2.5°	1087.5
5°	1075.5
7.5°	1056.3
10°	1026.8
12.5°	985.2
15°	930.9
17.5°	862.2
20°	781.5
22.5°	691.2
25°	595.3
27.5°	497.0
30°	403.5
32.5°	318.8
35°	246.1
37.5°	187.0
40°	138.2
42.5°	99.1
45°	71.9
47.5°	51.9
50°	35.2
52.5°	20.0
55°	11.2
57.5°	9.6
60°	8.8
62.5°	8.0
65°	7.2
67.5°	6.4
70°	5.6
72.5°	4.8
75°	4.0
77.5°	3.2
80°	2.4
82.5°	1.6
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)