

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259734

Luminaire Tested: P3AS09R609050DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259734
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609050DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 958.0 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259734

CATALOG NUMBER: P3AS09R609050DE010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1259734

CATALOG NUMBER: P3AS09R609050DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71
8	81	71	65	61	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	61	57		64
10	73	64	58	54	72	63	58	54	63	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	251011
5°	236957
10°	230791
15°	225518
20°	209692
25°	187462
30°	143187
35°	82663
40°	32089
45°	13366
50°	2934
55°	459
60°	351
65°	208
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13366 cd/sqm

TEST NUMBER: P1259734

CATALOG NUMBER: P3AS09R609050DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.6	10.6
10°-20°	276.7	28.9
20°-30°	346.6	36.2
30°-40°	193.8	20.2
40°-50°	36.8	3.8
50°-60°	1.9	0.2
60°-70°	0.4	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	724.9	75.7
0°-40°	918.7	95.9
0°-60°	957.4	99.9
0°-90°	958.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	958.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1145	
5°	1076	102
15°	993	277
25°	775	347
35°	309	194
45°	43	37
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1259734

CATALOG NUMBER: P3AS09R609050DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1144.7
1°	1140.0
2°	1125.1
3°	1107.5
4°	1091.0
5°	1076.5
6°	1065.5
7°	1056.1
8°	1049.1
9°	1042.4
10°	1036.5
11°	1030.7
12°	1024.0
13°	1015.8
14°	1006.0
15°	993.4
16°	978.1
17°	960.9
18°	941.3
19°	919.0
20°	898.6
21°	876.6
22°	853.9
23°	830.0
24°	803.8
25°	774.8
26°	740.7
27°	702.6
28°	659.9
29°	614.5
30°	565.5
31°	516.1
32°	465.2
32.5°	437.3
33°	412.3
34°	360.1
35°	308.8
36°	262.6
37°	213.6
37.5°	191.2
38°	169.3
39°	136.4
40°	112.1
42.5°	68.2
45°	43.1



TEST NUMBER: P1259734
CATALOG NUMBER: P3AS09R609050DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	23.9
50°	8.6
52.5°	2.0
55°	1.2
57.5°	0.8
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)