

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259031

Luminaire Tested: P3AS02R609050DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259031
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609050DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 280.0 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259031

CATALOG NUMBER: P3AS02R609050DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1259031

CATALOG NUMBER: P3AS02R609050DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		67
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66113
5°	65485
10°	63593
15°	59569
20°	52715
25°	44107
30°	34562
35°	25083
40°	16688
45°	10389
50°	5629
55°	1644
60°	1535
65°	1401
70°	1346
75°	1356
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10389 cd/sqm

TEST NUMBER: P1259031

CATALOG NUMBER: P3AS02R609050DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.0	10.0
10°-20°	72.8	26.0
20°-30°	83.0	29.6
30°-40°	58.8	21.0
40°-50°	26.7	9.5
50°-60°	5.7	2.0
60°-70°	2.7	1.0
70°-80°	1.7	0.6
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	183.8	65.6
0°-40°	242.6	86.6
0°-60°	275.0	98.2
0°-90°	280.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	280.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	302	
5°	298	28
15°	262	73
25°	182	83
35°	94	59
45°	34	27
55°	4	6
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1259031

CATALOG NUMBER: P3AS02R609050DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	301.5
2.5°	300.5
5°	297.5
7.5°	292.5
10°	285.6
12.5°	275.7
15°	262.4
17.5°	245.6
20°	225.9
22.5°	204.6
25°	182.3
27.5°	159.4
30°	136.5
32.5°	114.7
35°	93.7
37.5°	75.0
40°	58.3
42.5°	44.2
45°	33.5
47.5°	25.0
50°	16.5
52.5°	7.7
55°	4.3
57.5°	3.7
60°	3.5
62.5°	3.2
65°	2.7
67.5°	2.4
70°	2.1
72.5°	1.9
75°	1.6
77.5°	1.3
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)