

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259032

Luminaire Tested: P3AS02R609050DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259032
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609050DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 194.0 lumens
Efficiency: N/A
Efficacy: 53.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259032

CATALOG NUMBER: P3AS02R609050DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1259032

CATALOG NUMBER: P3AS02R609050DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49163
5°	48052
10°	45000
15°	40363
20°	34723
25°	28695
30°	22687
35°	16838
40°	11593
45°	7288
50°	3991
55°	2332
60°	2105
65°	1816
70°	1539
75°	1610
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7288 cd/sqm

TEST NUMBER: P1259032

CATALOG NUMBER: P3AS02R609050DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.3	10.5
10°-20°	49.4	25.5
20°-30°	54.2	27.9
30°-40°	39.5	20.3
40°-50°	18.7	9.6
50°-60°	6.1	3.1
60°-70°	3.5	1.8
70°-80°	1.9	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	123.9	63.9
0°-40°	163.4	84.2
0°-60°	188.1	97.0
0°-90°	194.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	194.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	224	
5°	218	20
15°	178	49
25°	119	54
35°	63	39
45°	24	19
55°	6	6
65°	4	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1259032

CATALOG NUMBER: P3AS02R609050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	224.2
2.5°	222.9
5°	218.3
7.5°	211.4
10°	202.1
12.5°	190.9
15°	177.8
17.5°	163.7
20°	148.8
22.5°	133.6
25°	118.6
27.5°	103.7
30°	89.6
32.5°	76.0
35°	62.9
37.5°	51.2
40°	40.5
42.5°	31.2
45°	23.5
47.5°	17.1
50°	11.7
52.5°	7.7
55°	6.1
57.5°	5.3
60°	4.8
62.5°	4.0
65°	3.5
67.5°	2.9
70°	2.4
72.5°	2.1
75°	1.9
77.5°	1.3
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)