

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259037

Luminaire Tested: P3AS02R659050DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259037
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659050DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 329.0 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259037

CATALOG NUMBER: P3AS02R659050DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1259037

CATALOG NUMBER: P3AS02R659050DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		87
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		60	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80410
5°	75677
10°	74704
15°	73394
20°	69283
25°	64310
30°	49982
35°	28911
40°	11650
45°	5365
50°	2081
55°	803
60°	702
65°	675
70°	705
75°	678
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5365 cd/sqm

TEST NUMBER: P1259037

CATALOG NUMBER: P3AS02R659050DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.7	9.9
10°-20°	90.3	27.4
20°-30°	118.2	35.9
30°-40°	68.4	20.8
40°-50°	14.6	4.5
50°-60°	2.4	0.7
60°-70°	1.3	0.4
70°-80°	0.8	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	241.1	73.3
0°-40°	309.6	94.1
0°-60°	326.6	99.3
0°-90°	329.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	329.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	367	
5°	344	33
15°	323	90
25°	266	118
35°	108	68
45°	17	15
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1259037

CATALOG NUMBER: P3AS02R659050DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	366.7
2.5°	356.3
5°	343.8
7.5°	338.7
10°	335.5
12.5°	331.0
15°	323.3
17.5°	311.3
20°	296.9
22.5°	283.4
25°	265.8
27.5°	236.3
30°	197.4
32.5°	153.0
35°	108.0
37.5°	68.4
40°	40.7
42.5°	25.5
45°	17.3
47.5°	11.2
50°	6.1
52.5°	2.9
55°	2.1
57.5°	1.9
60°	1.6
62.5°	1.6
65°	1.3
67.5°	1.1
70°	1.1
72.5°	0.8
75°	0.8
77.5°	0.5
80°	0.5
82.5°	0.3
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)