

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259766

Luminaire Tested: P3AS09R659050DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1259766  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R659050DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 802.0 lumens  
Efficiency: N/A  
Efficacy: 72.3 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1259766  
CATALOG NUMBER: P3AS09R659050DE010 E3DL1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1259766  
 CATALOG NUMBER: P3AS09R659050DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63				63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58				58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48				48

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	189130
5°	186858
10°	179778
15°	168401
20°	151470
25°	128620
30°	100598
35°	71688
40°	46916
45°	28995
50°	14737
55°	5199
60°	4561
65°	4566
70°	4103
75°	4067
80°	4041
85°	4026

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 28995 cd/sqm



TEST NUMBER: P1259766  
 CATALOG NUMBER: P3AS09R659050DE010 E3DL1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.7	9.9
10°-20°	206.5	25.7
20°-30°	241.3	30.1
30°-40°	168.6	21.0
40°-50°	74.2	9.3
50°-60°	16.5	2.1
60°-70°	8.4	1.0
70°-80°	5.1	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.4	65.8
0°-40°	696.0	86.8
0°-60°	786.8	98.1
0°-90°	802.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	802.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	862	
5°	849	80
15°	742	206
25°	532	241
35°	268	169
45°	94	74
55°	14	17
65°	9	8
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1259766  
CATALOG NUMBER: P3AS09R659050DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	862.5
2.5°	859.3
5°	848.9
7.5°	831.3
10°	807.4
12.5°	777.8
15°	741.8
17.5°	697.9
20°	649.1
22.5°	593.9
25°	531.6
27.5°	466.0
30°	397.3
32.5°	330.9
35°	267.8
37.5°	212.6
40°	163.9
42.5°	123.9
45°	93.5
47.5°	68.7
50°	43.2
52.5°	22.4
55°	13.6
57.5°	12.0
60°	10.4
62.5°	9.6
65°	8.8
67.5°	7.2
70°	6.4
72.5°	5.6
75°	4.8
77.5°	4.0
80°	3.2
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)