

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259055

Luminaire Tested: P3AS02R659050DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259055
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659050DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 210.0 lumens
Efficiency: N/A
Efficacy: 58.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259055

CATALOG NUMBER: P3AS02R659050DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1259055

CATALOG NUMBER: P3AS02R659050DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37365
5°	36870
10°	35626
15°	33598
20°	30989
25°	28139
30°	24915
35°	21201
40°	16860
45°	11908
50°	6925
55°	3785
60°	3508
65°	3165
70°	2885
75°	2711
80°	2399
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11908 cd/sqm

TEST NUMBER: P1259055

CATALOG NUMBER: P3AS02R659050DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.8	7.5
10°-20°	41.4	19.7
20°-30°	53.2	25.4
30°-40°	49.2	23.4
40°-50°	29.7	14.2
50°-60°	10.1	4.8
60°-70°	6.1	2.9
70°-80°	3.5	1.6
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	110.4	52.6
0°-40°	159.6	76.0
0°-60°	199.5	95.0
0°-90°	210.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	210.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	170	
5°	168	16
15°	148	41
25°	116	53
35°	79	49
45°	38	30
55°	10	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1259055

CATALOG NUMBER: P3AS02R659050DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	170.4
2.5°	169.6
5°	167.5
7.5°	164.3
10°	160.0
12.5°	154.7
15°	148.0
17.5°	140.8
20°	132.8
22.5°	124.6
25°	116.3
27.5°	107.5
30°	98.4
32.5°	89.3
35°	79.2
37.5°	69.3
40°	58.9
42.5°	48.5
45°	38.4
47.5°	29.1
50°	20.3
52.5°	12.8
55°	9.9
57.5°	8.8
60°	8.0
62.5°	6.9
65°	6.1
67.5°	5.3
70°	4.5
72.5°	4.0
75°	3.2
77.5°	2.7
80°	1.9
82.5°	1.3
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)