

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259060

Luminaire Tested: P3AS02R659050DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259060
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659050DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 267.0 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259060
CATALOG NUMBER: P3AS02R659050DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1259060
 CATALOG NUMBER: P3AS02R659050DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63				63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58				58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48				48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62955
5°	62205
10°	59852
15°	56073
20°	50428
25°	42825
30°	33499
35°	23878
40°	15629
45°	9644
50°	4912
55°	1720
60°	1535
65°	1505
70°	1346
75°	1356
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9644 cd/sqm



TEST NUMBER: P1259060
 CATALOG NUMBER: P3AS02R659050DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.5	9.9
10°-20°	68.7	25.7
20°-30°	80.3	30.1
30°-40°	56.2	21.0
40°-50°	24.7	9.2
50°-60°	5.5	2.1
60°-70°	2.8	1.0
70°-80°	1.7	0.6
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	175.6	65.8
0°-40°	231.8	86.8
0°-60°	262.0	98.1
0°-90°	267.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	267.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	287	
5°	283	27
15°	247	69
25°	177	80
35°	89	56
45°	31	25
55°	4	6
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1259060
CATALOG NUMBER: P3AS02R659050DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	287.1
2.5°	286.1
5°	282.6
7.5°	276.8
10°	268.8
12.5°	258.9
15°	247.0
17.5°	232.3
20°	216.1
22.5°	197.7
25°	177.0
27.5°	155.2
30°	132.3
32.5°	110.2
35°	89.2
37.5°	70.8
40°	54.6
42.5°	41.2
45°	31.1
47.5°	22.9
50°	14.4
52.5°	7.5
55°	4.5
57.5°	4.0
60°	3.5
62.5°	3.2
65°	2.9
67.5°	2.4
70°	2.1
72.5°	1.9
75°	1.6
77.5°	1.3
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)