

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259801

Luminaire Tested: P3AS09R709050DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259801
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709050DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R70 optic, 5000K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 575.0 lumens
Efficiency: N/A
Efficacy: 51.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259801
CATALOG NUMBER: P3AS09R709050DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1259801
 CATALOG NUMBER: P3AS09R709050DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	134880
5°	132401
10°	124847
15°	113304
20°	99105
25°	83594
30°	68441
35°	53110
40°	38014
45°	24065
50°	12008
55°	7340
60°	6315
65°	5811
70°	5129
75°	4745
80°	4041
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24065 cd/sqm



TEST NUMBER: P1259801
 CATALOG NUMBER: P3AS09R709050DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.1	9.8
10°-20°	138.9	24.2
20°-30°	158.1	27.5
30°-40°	123.7	21.5
40°-50°	60.8	10.6
50°-60°	18.7	3.3
60°-70°	11.1	1.9
70°-80°	5.9	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.2	61.4
0°-40°	476.8	82.9
0°-60°	556.3	96.7
0°-90°	575.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	575.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	615	
5°	602	56
15°	499	139
25°	346	158
35°	198	124
45°	78	61
55°	19	19
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1259801
CATALOG NUMBER: P3AS09R709050DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	615.1
2.5°	611.9
5°	601.5
7.5°	584.7
10°	560.7
12.5°	532.7
15°	499.1
17.5°	463.1
20°	424.7
22.5°	384.7
25°	345.5
27.5°	307.1
30°	270.3
32.5°	233.5
35°	198.4
37.5°	164.8
40°	132.8
42.5°	103.2
45°	77.6
47.5°	54.4
50°	35.2
52.5°	23.2
55°	19.2
57.5°	16.8
60°	14.4
62.5°	12.8
65°	11.2
67.5°	9.6
70°	8.0
72.5°	6.4
75°	5.6
77.5°	4.8
80°	3.2
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)