

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259073

Luminaire Tested: P3AS02R709050DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1259073  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R709050DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R70 optic, 5000K CCT AND, 90CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 131.1 lumens  
Efficiency: N/A  
Efficacy: 36.4 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1259073  
CATALOG NUMBER: P3AS02R709050DE010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1259073

CATALOG NUMBER: P3AS02R709050DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	68	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	47	47	47	47
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	25371
5°	25049
10°	24337
15°	23292
20°	21819
25°	19840
30°	17117
35°	13652
40°	9933
45°	6543
50°	3070
55°	956
60°	921
65°	882
70°	833
75°	847
80°	884
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6543 cd/sqm



TEST NUMBER: P1259073  
 CATALOG NUMBER: P3AS02R709050DE010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	10.7	8.2
10°-20°	28.7	21.9
20°-30°	37.3	28.5
30°-40°	31.7	24.2
40°-50°	16.3	12.5
50°-60°	3.1	2.4
60°-70°	1.7	1.3
70°-80°	1.1	0.8
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	76.8	58.6
0°-40°	108.5	82.8
0°-60°	128.0	97.6
0°-90°	131.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	131.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	116	
5°	114	11
15°	103	29
25°	82	37
35°	51	32
45°	21	16
55°	2	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1259073  
CATALOG NUMBER: P3AS02R709050DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	115.7
2.5°	115.3
5°	113.8
7.5°	111.8
10°	109.3
12.5°	106.2
15°	102.6
17.5°	98.4
20°	93.5
22.5°	88.1
25°	82.0
27.5°	75.1
30°	67.6
32.5°	59.5
35°	51.0
37.5°	42.7
40°	34.7
42.5°	27.3
45°	21.1
47.5°	15.5
50°	9.0
52.5°	3.9
55°	2.5
57.5°	2.3
60°	2.1
62.5°	2.0
65°	1.7
67.5°	1.6
70°	1.3
72.5°	1.2
75°	1.0
77.5°	0.8
80°	0.7
82.5°	0.4
85°	0.3
87.5°	0.1
90°	0.0

(END OF REPORT)