

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259804

Luminaire Tested: P3AS09R709050DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259804
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709050DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R70 optic, 5000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 805.0 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259804

CATALOG NUMBER: P3AS09R709050DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1259804

CATALOG NUMBER: P3AS09R709050DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	155843
5°	153973
10°	149518
15°	143179
20°	134132
25°	121846
30°	105257
35°	83895
40°	61086
45°	40159
50°	18831
55°	5811
60°	5614
65°	5396
70°	5129
75°	5422
80°	5051
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 40159 cd/sqm

TEST NUMBER: P1259804

CATALOG NUMBER: P3AS09R709050DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	8.2
10°-20°	176.5	21.9
20°-30°	229.4	28.5
30°-40°	194.7	24.2
40°-50°	100.4	12.5
50°-60°	19.4	2.4
60°-70°	10.5	1.3
70°-80°	6.4	0.8
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	471.8	58.6
0°-40°	666.5	82.8
0°-60°	786.2	97.7
0°-90°	805.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	805.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	711	
5°	700	66
15°	631	177
25°	504	229
35°	313	195
45°	130	100
55°	15	19
65°	10	10
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1259804

CATALOG NUMBER: P3AS09R709050DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	710.7
2.5°	708.3
5°	699.5
7.5°	686.7
10°	671.5
12.5°	652.3
15°	630.7
17.5°	604.4
20°	574.8
22.5°	541.2
25°	503.6
27.5°	461.3
30°	415.7
32.5°	365.3
35°	313.4
37.5°	262.2
40°	213.4
42.5°	167.9
45°	129.5
47.5°	95.1
50°	55.2
52.5°	24.0
55°	15.2
57.5°	14.4
60°	12.8
62.5°	12.0
65°	10.4
67.5°	9.6
70°	8.0
72.5°	7.2
75°	6.4
77.5°	4.8
80°	4.0
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)