

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259141

Luminaire Tested: P3AS05R159050DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259141
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159050DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 5000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 165.0 lumens
Efficiency: N/A
Efficacy: 22.9 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259141

CATALOG NUMBER: P3AS05R159050DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1259141

CATALOG NUMBER: P3AS05R159050DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71157
5°	65771
10°	52504
15°	39660
20°	30196
25°	23009
30°	16484
35°	10761
40°	6584
45°	4000
50°	2661
55°	2064
60°	1754
65°	1505
70°	1346
75°	1356
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4000 cd/sqm

TEST NUMBER: P1259141

CATALOG NUMBER: P3AS05R159050DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.5	16.0
10°-20°	48.8	29.6
20°-30°	43.5	26.3
30°-40°	25.7	15.6
40°-50°	10.5	6.4
50°-60°	5.0	3.0
60°-70°	3.0	1.8
70°-80°	1.6	1.0
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	118.8	72.0
0°-40°	144.5	87.6
0°-60°	160.0	97.0
0°-90°	165.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	165.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	324	
5°	299	26
15°	175	49
25°	95	43
35°	40	26
45°	13	11
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1259141

CATALOG NUMBER: P3AS05R159050DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	324.5
1°	323.7
2°	321.3
3°	316.4
4°	308.4
5°	298.8
6°	288.3
7°	276.0
8°	263.1
9°	250.0
10°	235.8
12.5°	203.4
15°	174.7
17.5°	150.0
20°	129.4
22.5°	111.2
25°	95.1
27.5°	79.6
30°	65.1
32.5°	52.0
35°	40.2
37.5°	30.8
40°	23.0
42.5°	17.1
45°	12.9
47.5°	9.9
50°	7.8
52.5°	6.4
55°	5.4
57.5°	4.6
60°	4.0
62.5°	3.5
65°	2.9
67.5°	2.7
70°	2.1
72.5°	1.9
75°	1.6
77.5°	1.1
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)