

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259893

Luminaire Tested: P3AS13R159050DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259893
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R159050DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 5000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 320.0 lumens
Efficiency: N/A
Efficacy: 21.9 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259893

CATALOG NUMBER: P3AS13R159050DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1259893

CATALOG NUMBER: P3AS13R159050DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	137993
5°	127537
10°	101824
15°	76913
20°	58572
25°	44640
30°	31980
35°	20853
40°	12795
45°	7722
50°	5151
55°	3976
60°	3421
65°	2958
70°	2693
75°	2626
80°	2020
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7722 cd/sqm

TEST NUMBER: P1259893

CATALOG NUMBER: P3AS13R159050DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.3	16.0
10°-20°	94.7	29.6
20°-30°	84.3	26.3
30°-40°	49.9	15.6
40°-50°	20.5	6.4
50°-60°	9.6	3.0
60°-70°	5.9	1.8
70°-80°	3.1	1.0
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	230.3	72.0
0°-40°	280.2	87.6
0°-60°	310.3	97.0
0°-90°	320.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	320.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	629	
5°	579	51
15°	339	95
25°	184	84
35°	78	50
45°	25	20
55°	10	10
65°	6	6
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1259893

CATALOG NUMBER: P3AS13R159050DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	629.3
1°	627.7
2°	623.1
3°	613.7
4°	598.1
5°	579.4
6°	559.1
7°	535.2
8°	510.3
9°	484.8
10°	457.3
12.5°	394.4
15°	338.8
17.5°	291.0
20°	251.0
22.5°	215.7
25°	184.5
27.5°	154.3
30°	126.3
32.5°	100.8
35°	77.9
37.5°	59.8
40°	44.7
42.5°	33.3
45°	24.9
47.5°	19.2
50°	15.1
52.5°	12.5
55°	10.4
57.5°	8.8
60°	7.8
62.5°	6.8
65°	5.7
67.5°	5.2
70°	4.2
72.5°	3.6
75°	3.1
77.5°	2.1
80°	1.6
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)