

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259187

Luminaire Tested: P3AS05R259050DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259187
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259050DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 281.0 lumens
Efficiency: N/A
Efficacy: 39.0 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259187

CATALOG NUMBER: P3AS05R259050DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1259187

CATALOG NUMBER: P3AS05R259050DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	180249
5°	168170
10°	134711
15°	91442
20°	55328
25°	32349
30°	18433
35°	10146
40°	5382
45°	2822
50°	1637
55°	1223
60°	1053
65°	1090
70°	1026
75°	932
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2822 cd/sqm

TEST NUMBER: P1259187

CATALOG NUMBER: P3AS05R259050DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.8	24.1
10°-20°	110.7	39.4
20°-30°	63.3	22.5
30°-40°	25.0	8.9
40°-50°	7.6	2.7
50°-60°	3.0	1.1
60°-70°	2.0	0.7
70°-80°	1.1	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	241.8	86.1
0°-40°	266.8	95.0
0°-60°	277.5	98.8
0°-90°	281.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	281.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	822	
5°	764	68
15°	403	111
25°	134	63
35°	38	25
45°	9	8
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1259187

CATALOG NUMBER: P3AS05R259050DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	822.0
1°	820.4
2°	813.7
3°	801.9
4°	785.5
5°	764.0
6°	738.8
7°	710.3
8°	677.3
9°	643.4
10°	605.0
11°	567.2
12°	525.5
13°	484.5
14°	442.3
15°	402.8
17.5°	312.3
20°	237.1
22.5°	178.0
25°	133.7
27.5°	99.1
30°	72.8
32.5°	52.6
35°	37.9
37.5°	26.9
40°	18.8
42.5°	12.9
45°	9.1
47.5°	6.4
50°	4.8
52.5°	3.8
55°	3.2
57.5°	3.0
60°	2.4
62.5°	2.1
65°	2.1
67.5°	1.9
70°	1.6
72.5°	1.3
75°	1.1
77.5°	0.8
80°	0.5
82.5°	0.5
85°	0.3
87.5°	0.3



TEST NUMBER: P1259187
CATALOG NUMBER: P3AS05R259050DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)