

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259946

Luminaire Tested: P3AS13R259050DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259946
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259050DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 852.0 lumens
Efficiency: N/A
Efficacy: 58.4 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259946

CATALOG NUMBER: P3AS13R259050DE010 E3DLD1H

Luminous Intensity Polar Plot



TEST NUMBER: P1259946

CATALOG NUMBER: P3AS13R259050DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202484
5°	197666
10°	183163
15°	163134
20°	140199
25°	119160
30°	98091
35°	76426
40°	54989
45°	34887
50°	20639
55°	14183
60°	13025
65°	12141
70°	10899
75°	9913
80°	9345
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34887 cd/sqm

TEST NUMBER: P1259946

CATALOG NUMBER: P3AS13R259050DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.3	9.8
10°-20°	199.5	23.4
20°-30°	225.4	26.5
30°-40°	178.3	20.9
40°-50°	90.1	10.6
50°-60°	36.1	4.2
60°-70°	23.1	2.7
70°-80°	12.8	1.5
80°-90°	3.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	508.2	59.6
0°-40°	686.4	80.6
0°-60°	812.6	95.4
0°-90°	852.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	852.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	923	
5°	898	83
15°	719	199
25°	492	225
35°	286	178
45°	112	90
55°	37	36
65°	23	23
75°	12	13
85°	3	4
90°	0	

TEST NUMBER: P1259946

CATALOG NUMBER: P3AS13R259050DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	923.4
1°	923.4
2°	920.2
3°	914.9
4°	907.5
5°	898.0
6°	886.3
7°	872.5
8°	857.6
9°	840.6
10°	822.6
11°	802.4
12°	783.3
13°	761.0
14°	739.8
15°	718.6
17.5°	659.1
20°	600.8
22.5°	545.6
25°	492.5
27.5°	440.5
30°	387.4
32.5°	337.5
35°	285.5
37.5°	237.8
40°	192.1
42.5°	149.7
45°	112.5
47.5°	83.9
50°	60.5
52.5°	45.6
55°	37.1
57.5°	34.0
60°	29.7
62.5°	26.5
65°	23.4
67.5°	20.2
70°	17.0
72.5°	14.9
75°	11.7
77.5°	9.6
80°	7.4
82.5°	5.3
85°	3.2
87.5°	1.1



TEST NUMBER: P1259946

CATALOG NUMBER: P3AS13R259050DE010 E3DLD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)