

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259959

Luminaire Tested: P3AS13R259050DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259959
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259050DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 612.0 lumens
Efficiency: N/A
Efficacy: 41.9 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259959
CATALOG NUMBER: P3AS13R259050DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1259959
 CATALOG NUMBER: P3AS13R259050DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68	68	68	68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59	59	59	59
7	79	69	63	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	205641
5°	194276
10°	165127
15°	130784
20°	99409
25°	74158
30°	53932
35°	38146
40°	25877
45°	18048
50°	15147
55°	14642
60°	15437
65°	15877
70°	15708
75°	16860
80°	19321
85°	19373

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 20664 cd/sqm



TEST NUMBER: P1259959
 CATALOG NUMBER: P3AS13R259050DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.7	13.0
10°-20°	159.5	26.1
20°-30°	141.2	23.1
30°-40°	89.9	14.7
40°-50°	47.6	7.8
50°-60°	35.0	5.7
60°-70°	29.8	4.9
70°-80°	21.0	3.4
80°-90°	8.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.3	62.1
0°-40°	470.3	76.8
0°-60°	552.8	90.3
0°-90°	612.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	612.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	938	
5°	883	80
15°	576	159
25°	306	141
35°	142	90
45°	58	48
55°	38	35
65°	31	30
75°	20	21
85°	8	8
90°	0	



TEST NUMBER: P1259959
CATALOG NUMBER: P3AS13R259050DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	937.8
2.5°	924.0
5°	882.6
7.5°	818.2
10°	741.6
12.5°	658.9
15°	576.1
17.5°	496.5
20°	426.0
22.5°	361.6
25°	306.5
27.5°	257.4
30°	213.0
32.5°	174.7
35°	142.5
37.5°	113.4
40°	90.4
42.5°	72.0
45°	58.2
47.5°	50.6
50°	44.4
52.5°	41.4
55°	38.3
57.5°	36.8
60°	35.2
62.5°	32.2
65°	30.6
67.5°	27.6
70°	24.5
72.5°	23.0
75°	19.9
77.5°	16.9
80°	15.3
82.5°	12.3
85°	7.7
87.5°	3.1
90°	0.0

(END OF REPORT)