

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260009

Luminaire Tested: P3AS13R359050DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359050DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 5000K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 859.0 lumens
Efficiency: N/A
Efficacy: 58.8 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260009
CATALOG NUMBER: P3AS13R359050DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1260009

CATALOG NUMBER: P3AS13R359050DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	196212
5°	192053
10°	179868
15°	161454
20°	140456
25°	119692
30°	100243
35°	79853
40°	57737
45°	36531
50°	19923
55°	13801
60°	13025
65°	12141
70°	11540
75°	9913
80°	9345
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 36531 cd/sqm



TEST NUMBER: P1260009
 CATALOG NUMBER: P3AS13R359050DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	9.5
10°-20°	197.9	23.0
20°-30°	226.8	26.4
30°-40°	185.1	21.5
40°-50°	93.3	10.9
50°-60°	34.7	4.0
60°-70°	23.2	2.7
70°-80°	12.9	1.5
80°-90°	3.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	505.9	58.9
0°-40°	691.0	80.4
0°-60°	819.0	95.3
0°-90°	859.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	859.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	895	
5°	872	81
15°	711	198
25°	495	227
35°	298	185
45°	118	93
55°	36	35
65°	23	23
75°	12	13
85°	3	4
90°	0	



TEST NUMBER: P1260009
CATALOG NUMBER: P3AS13R359050DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	894.8
1°	893.8
2°	891.7
3°	887.4
4°	881.0
5°	872.5
6°	861.9
7°	851.3
8°	837.5
9°	823.7
10°	807.8
11°	790.8
12°	772.8
13°	752.6
14°	731.4
15°	711.2
17.5°	657.1
20°	601.9
22.5°	545.6
25°	494.7
27.5°	444.8
30°	395.9
32.5°	347.1
35°	298.3
37.5°	249.5
40°	201.7
42.5°	157.1
45°	117.8
47.5°	84.9
50°	58.4
52.5°	42.5
55°	36.1
57.5°	32.9
60°	29.7
62.5°	26.5
65°	23.4
67.5°	20.2
70°	18.0
72.5°	14.9
75°	11.7
77.5°	9.6
80°	7.4
82.5°	5.3
85°	3.2
87.5°	2.1



TEST NUMBER: P1260009
CATALOG NUMBER: P3AS13R359050DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)