

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259262

Luminaire Tested: P3AS05R359050DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259262
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359050DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 5000K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 355.0 lumens
Efficiency: N/A
Efficacy: 49.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259262

CATALOG NUMBER: P3AS05R359050DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1259262

CATALOG NUMBER: P3AS05R359050DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114114
5°	111292
10°	101757
15°	86357
20°	68373
25°	51705
30°	37651
35°	25458
40°	15658
45°	8993
50°	5424
55°	4396
60°	3815
65°	3424
70°	2821
75°	2796
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8993 cd/sqm

TEST NUMBER: P1259262

CATALOG NUMBER: P3AS05R359050DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	13.2
10°-20°	104.9	29.5
20°-30°	98.1	27.6
30°-40°	60.1	16.9
40°-50°	23.7	6.7
50°-60°	10.4	2.9
60°-70°	6.5	1.8
70°-80°	3.5	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	249.7	70.3
0°-40°	309.8	87.3
0°-60°	343.9	96.9
0°-90°	355.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	355.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	520	
5°	506	47
15°	380	105
25°	214	98
35°	95	60
45°	29	24
55°	12	10
65°	7	7
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1259262

CATALOG NUMBER: P3AS05R359050DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	520.4
1°	520.9
2°	519.3
3°	516.0
4°	511.1
5°	505.6
6°	498.5
7°	490.3
8°	480.5
9°	469.5
10°	457.0
11°	443.8
12°	429.6
13°	414.3
14°	397.4
15°	380.4
17.5°	336.7
20°	293.0
22.5°	250.9
25°	213.7
27.5°	179.3
30°	148.7
32.5°	120.3
35°	95.1
37.5°	72.7
40°	54.7
42.5°	39.4
45°	29.0
47.5°	20.8
50°	15.9
52.5°	13.1
55°	11.5
57.5°	9.8
60°	8.7
62.5°	7.7
65°	6.6
67.5°	5.5
70°	4.4
72.5°	3.8
75°	3.3
77.5°	2.7
80°	2.2
82.5°	1.6
85°	1.1
87.5°	0.5



TEST NUMBER: P1259262
CATALOG NUMBER: P3AS05R359050DE010 E3DLP1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)