

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260037

Luminaire Tested: P3AS13R409050DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260037
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409050DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 5000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 465.0 lumens
Efficiency: N/A
Efficacy: 31.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260037
CATALOG NUMBER: P3AS13R409050DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1260037
 CATALOG NUMBER: P3AS13R409050DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104378
5°	102487
10°	96614
15°	87742
20°	77100
25°	65834
30°	54540
35°	42054
40°	29942
45°	20157
50°	11019
55°	7761
60°	7280
65°	6745
70°	6027
75°	5761
80°	4546
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20157 cd/sqm



TEST NUMBER: P1260037
 CATALOG NUMBER: P3AS13R409050DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.4	9.3
10°-20°	107.7	23.2
20°-30°	124.5	26.8
30°-40°	98.1	21.1
40°-50°	50.3	10.8
50°-60°	19.3	4.1
60°-70°	12.7	2.7
70°-80°	6.9	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	275.6	59.3
0°-40°	373.7	80.4
0°-60°	443.3	95.3
0°-90°	465.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	465.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	476	
5°	466	43
15°	386	108
25°	272	124
35°	157	98
45°	65	50
55°	20	19
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1260037
CATALOG NUMBER: P3AS13R409050DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	476.0
2.5°	473.4
5°	465.6
7.5°	452.1
10°	433.9
12.5°	412.6
15°	386.5
17.5°	359.5
20°	330.4
22.5°	300.7
25°	272.1
27.5°	243.5
30°	215.4
32.5°	186.8
35°	157.1
37.5°	129.5
40°	104.6
42.5°	83.2
45°	65.0
47.5°	47.3
50°	32.3
52.5°	23.4
55°	20.3
57.5°	18.2
60°	16.6
62.5°	14.6
65°	13.0
67.5°	10.9
70°	9.4
72.5°	7.8
75°	6.8
77.5°	5.2
80°	3.6
82.5°	3.1
85°	1.6
87.5°	1.0
90°	0.0

(END OF REPORT)