

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259264

Luminaire Tested: P3AS05R359050DE010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1259264  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R359050DE010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R35 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 355.0 lumens  
Efficiency: N/A  
Efficacy: 49.3 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1259264

CATALOG NUMBER: P3AS05R359050DE010 E3DLP1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1259264

CATALOG NUMBER: P3AS05R359050DE010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 97  | 93  | 97  | 94  | 91  |  | 94  | 92  | 89  |  | 91  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 85  | 91  | 87  | 84  |  | 89  | 85  | 82  |  | 86  |
| 4   | 97  | 89  | 83  | 79  | 95  | 88  | 82  | 78  | 86  | 81  | 77  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 83  | 77  | 73  | 90  | 82  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 71  |  | 77  |
| 6   | 87  | 78  | 72  | 68  | 86  | 77  | 72  | 68  | 76  | 71  | 67  |  | 75  | 70  | 67  |  | 73  |
| 7   | 83  | 74  | 68  | 63  | 82  | 73  | 67  | 63  | 72  | 67  | 63  |  | 71  | 66  | 63  |  | 69  |
| 8   | 79  | 70  | 64  | 60  | 78  | 69  | 63  | 59  | 68  | 63  | 59  |  | 67  | 62  | 59  |  | 66  |
| 9   | 76  | 66  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 59  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 61  | 56  | 53  |  | 61  | 56  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 114114 |
| 5°  | 111292 |
| 10° | 101757 |
| 15° | 86357  |
| 20° | 68373  |
| 25° | 51705  |
| 30° | 37651  |
| 35° | 25458  |
| 40° | 15658  |
| 45° | 8993   |
| 50° | 5424   |
| 55° | 4396   |
| 60° | 3815   |
| 65° | 3424   |
| 70° | 2821   |
| 75° | 2796   |
| 80° | 2778   |
| 85° | 2768   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 8993 cd/sqm

TEST NUMBER: P1259264

CATALOG NUMBER: P3AS05R359050DE010 E3DLP1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 46.7   | 13.2      |
| 10°-20°   | 104.9  | 29.5      |
| 20°-30°   | 98.1   | 27.6      |
| 30°-40°   | 60.1   | 16.9      |
| 40°-50°   | 23.7   | 6.7       |
| 50°-60°   | 10.4   | 2.9       |
| 60°-70°   | 6.5    | 1.8       |
| 70°-80°   | 3.5    | 1.0       |
| 80°-90°   | 1.2    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 249.7  | 70.3      |
| 0°-40°    | 309.8  | 87.3      |
| 0°-60°    | 343.9  | 96.9      |
| 0°-90°    | 355.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 355.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 520 |      |
| 5°  | 506 | 47   |
| 15° | 380 | 105  |
| 25° | 214 | 98   |
| 35° | 95  | 60   |
| 45° | 29  | 24   |
| 55° | 12  | 10   |
| 65° | 7   | 7    |
| 75° | 3   | 3    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1259264

CATALOG NUMBER: P3AS05R359050DE010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 520.4 |
| 1°    | 520.9 |
| 2°    | 519.3 |
| 3°    | 516.0 |
| 4°    | 511.1 |
| 5°    | 505.6 |
| 6°    | 498.5 |
| 7°    | 490.3 |
| 8°    | 480.5 |
| 9°    | 469.5 |
| 10°   | 457.0 |
| 11°   | 443.8 |
| 12°   | 429.6 |
| 13°   | 414.3 |
| 14°   | 397.4 |
| 15°   | 380.4 |
| 17.5° | 336.7 |
| 20°   | 293.0 |
| 22.5° | 250.9 |
| 25°   | 213.7 |
| 27.5° | 179.3 |
| 30°   | 148.7 |
| 32.5° | 120.3 |
| 35°   | 95.1  |
| 37.5° | 72.7  |
| 40°   | 54.7  |
| 42.5° | 39.4  |
| 45°   | 29.0  |
| 47.5° | 20.8  |
| 50°   | 15.9  |
| 52.5° | 13.1  |
| 55°   | 11.5  |
| 57.5° | 9.8   |
| 60°   | 8.7   |
| 62.5° | 7.7   |
| 65°   | 6.6   |
| 67.5° | 5.5   |
| 70°   | 4.4   |
| 72.5° | 3.8   |
| 75°   | 3.3   |
| 77.5° | 2.7   |
| 80°   | 2.2   |
| 82.5° | 1.6   |
| 85°   | 1.1   |
| 87.5° | 0.5   |



TEST NUMBER: P1259264

CATALOG NUMBER: P3AS05R359050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)