

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260041

Luminaire Tested: P3AS13R409050DE010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1260041  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R409050DE010 E3DLD1WH  
Description: 3in Adjustable LED luminaire with, R40 optic, 5000K CCT AND, 90CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 948.0 lumens  
Efficiency: N/A  
Efficacy: 64.9 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260041  
CATALOG NUMBER: P3AS13R409050DE010 E3DLD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1260041  
 CATALOG NUMBER: P3AS13R409050DE010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45				45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	212812
5°	208958
10°	196968
15°	178889
20°	157164
25°	134209
30°	111182
35°	85742
40°	61029
45°	41121
50°	22447
55°	15827
60°	14867
65°	13750
70°	12246
75°	11692
80°	9345
85°	8051

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 41121 cd/sqm



TEST NUMBER: P1260041  
 CATALOG NUMBER: P3AS13R409050DE010 E3DLD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.5	9.3
10°-20°	219.5	23.2
20°-30°	253.8	26.8
30°-40°	200.0	21.1
40°-50°	102.7	10.8
50°-60°	39.2	4.1
60°-70°	26.0	2.7
70°-80°	14.1	1.5
80°-90°	4.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	561.8	59.3
0°-40°	761.8	80.4
0°-60°	903.7	95.3
0°-90°	948.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	948.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	970	
5°	949	89
15°	788	220
25°	555	254
35°	320	200
45°	133	103
55°	41	39
65°	26	26
75°	14	14
85°	3	4
90°	0	



TEST NUMBER: P1260041  
CATALOG NUMBER: P3AS13R409050DE010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	970.5
2.5°	965.2
5°	949.3
7.5°	921.7
10°	884.6
12.5°	841.1
15°	788.0
17.5°	732.9
20°	673.5
22.5°	613.0
25°	554.7
27.5°	496.4
30°	439.1
32.5°	380.8
35°	320.3
37.5°	264.1
40°	213.2
42.5°	169.7
45°	132.6
47.5°	96.5
50°	65.8
52.5°	47.7
55°	41.4
57.5°	37.1
60°	33.9
62.5°	29.7
65°	26.5
67.5°	22.3
70°	19.1
72.5°	15.9
75°	13.8
77.5°	10.6
80°	7.4
82.5°	6.4
85°	3.2
87.5°	2.1
90°	0.0

(END OF REPORT)