

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259290

Luminaire Tested: P3AS05R409050DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259290
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409050DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 5000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 488.9 lumens
Efficiency: N/A
Efficacy: 67.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259290

CATALOG NUMBER: P3AS05R409050DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1259290

CATALOG NUMBER: P3AS05R409050DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109772
5°	107792
10°	101601
15°	92282
20°	81067
25°	69222
30°	57351
35°	44223
40°	31488
45°	21212
50°	11565
55°	8143
60°	7675
65°	7108
70°	6283
75°	6015
80°	4799
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21212 cd/sqm

TEST NUMBER: P1259290

CATALOG NUMBER: P3AS05R409050DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.7	9.3
10°-20°	113.2	23.2
20°-30°	130.9	26.8
30°-40°	103.2	21.1
40°-50°	53.0	10.8
50°-60°	20.2	4.1
60°-70°	13.4	2.7
70°-80°	7.3	1.5
80°-90°	2.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	289.8	59.3
0°-40°	392.9	80.4
0°-60°	466.1	95.3
0°-90°	488.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	488.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	501	
5°	490	46
15°	406	113
25°	286	131
35°	165	103
45°	68	53
55°	21	20
65°	14	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1259290

CATALOG NUMBER: P3AS05R409050DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	500.6
2.5°	497.9
5°	489.7
7.5°	475.4
10°	456.3
12.5°	433.8
15°	406.5
17.5°	378.0
20°	347.4
22.5°	316.2
25°	286.1
27.5°	256.0
30°	226.5
32.5°	196.4
35°	165.2
37.5°	136.2
40°	110.0
42.5°	87.5
45°	68.4
47.5°	49.8
50°	33.9
52.5°	24.6
55°	21.3
57.5°	19.1
60°	17.5
62.5°	15.3
65°	13.7
67.5°	11.5
70°	9.8
72.5°	8.2
75°	7.1
77.5°	5.5
80°	3.8
82.5°	3.3
85°	1.6
87.5°	1.1
90°	0.0

(END OF REPORT)