

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259310

Luminaire Tested: P3AS05R459050DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259310
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459050DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 232.9 lumens
Efficiency: N/A
Efficacy: 32.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259310

CATALOG NUMBER: P3AS05R459050DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1259310

CATALOG NUMBER: P3AS05R459050DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	91	85	81	88	83	80		85	81	78		83
4	94	85	79	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	50	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49404
5°	48536
10°	45913
15°	41884
20°	37033
25°	32155
30°	27599
35°	22995
40°	17146
45°	10482
50°	4844
55°	3785
60°	3640
65°	3321
70°	3077
75°	2965
80°	2652
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10482 cd/sqm

TEST NUMBER: P1259310

CATALOG NUMBER: P3AS05R459050DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.6	8.8
10°-20°	51.4	22.1
20°-30°	61.0	26.2
30°-40°	53.0	22.8
40°-50°	26.6	11.4
50°-60°	9.2	4.0
60°-70°	6.4	2.8
70°-80°	3.6	1.5
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	133.0	57.1
0°-40°	186.0	79.9
0°-60°	221.8	95.2
0°-90°	232.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	232.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	225	
5°	220	21
15°	184	51
25°	133	61
35°	86	53
45°	34	27
55°	10	9
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1259310

CATALOG NUMBER: P3AS05R459050DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	225.3
2.5°	224.2
5°	220.5
7.5°	214.5
10°	206.2
12.5°	196.0
15°	184.5
17.5°	171.6
20°	158.7
22.5°	145.5
25°	132.9
27.5°	120.8
30°	109.0
32.5°	97.7
35°	85.9
37.5°	73.3
40°	59.9
42.5°	46.7
45°	33.8
47.5°	22.3
50°	14.2
52.5°	11.0
55°	9.9
57.5°	9.1
60°	8.3
62.5°	7.5
65°	6.4
67.5°	5.6
70°	4.8
72.5°	4.0
75°	3.5
77.5°	2.7
80°	2.1
82.5°	1.6
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)