

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259313

Luminaire Tested: P3AS05R459050DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259313
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459050DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 474.0 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259313

CATALOG NUMBER: P3AS05R459050DE010 E3DLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1259313

CATALOG NUMBER: P3AS05R459050DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75		
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69		
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63		
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54		
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50		
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47		
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100496
5°	98723
10°	93407
15°	85199
20°	75327
25°	65423
30°	56161
35°	46793
40°	34865
45°	21336
50°	9893
55°	7723
60°	7412
65°	6797
70°	6283
75°	6015
80°	5556
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 21336 cd/sqm

TEST NUMBER: P1259313

CATALOG NUMBER: P3AS05R459050DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	8.8
10°-20°	104.5	22.0
20°-30°	124.1	26.2
30°-40°	107.9	22.8
40°-50°	54.1	11.4
50°-60°	18.8	4.0
60°-70°	13.2	2.8
70°-80°	7.4	1.6
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.5	57.1
0°-40°	378.4	79.8
0°-60°	451.2	95.2
0°-90°	474.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	474.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	458	
5°	448	42
15°	375	104
25°	270	124
35°	175	108
45°	69	54
55°	20	19
65°	13	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1259313

CATALOG NUMBER: P3AS05R459050DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	458.3
2.5°	456.1
5°	448.5
7.5°	436.5
10°	419.5
12.5°	398.8
15°	375.3
17.5°	349.1
20°	322.8
22.5°	296.1
25°	270.4
27.5°	245.8
30°	221.8
32.5°	198.8
35°	174.8
37.5°	149.1
40°	121.8
42.5°	95.0
45°	68.8
47.5°	45.3
50°	29.0
52.5°	22.4
55°	20.2
57.5°	18.6
60°	16.9
62.5°	15.3
65°	13.1
67.5°	11.5
70°	9.8
72.5°	8.2
75°	7.1
77.5°	5.5
80°	4.4
82.5°	3.3
85°	1.6
87.5°	1.1
90°	0.0

(END OF REPORT)