

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260097

Luminaire Tested: P3AS13R509050DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260097
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509050DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 5000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 384.0 lumens
Efficiency: N/A
Efficacy: 26.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260097

CATALOG NUMBER: P3AS13R509050DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1260097

CATALOG NUMBER: P3AS13R509050DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	111680
5°	108672
10°	100221
15°	88128
20°	73740
25°	58479
30°	42893
35°	29500
40°	18749
45°	10482
50°	5663
55°	4779
60°	4122
65°	3788
70°	3334
75°	3050
80°	2652
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10482 cd/sqm

TEST NUMBER: P1260097

CATALOG NUMBER: P3AS13R509050DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.7	11.9
10°-20°	107.5	28.0
20°-30°	110.0	28.6
30°-40°	69.7	18.2
40°-50°	27.8	7.2
50°-60°	11.2	2.9
60°-70°	7.2	1.9
70°-80°	3.7	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	263.2	68.6
0°-40°	333.0	86.7
0°-60°	372.0	96.9
0°-90°	384.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	384.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	509	
5°	494	46
15°	388	108
25°	242	110
35°	110	70
45°	34	28
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1260097

CATALOG NUMBER: P3AS13R509050DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	509.3
2.5°	505.7
5°	493.7
7.5°	475.0
10°	450.1
12.5°	420.5
15°	388.2
17.5°	352.9
20°	316.0
22.5°	279.1
25°	241.7
27.5°	204.2
30°	169.4
32.5°	138.2
35°	110.2
37.5°	86.3
40°	65.5
42.5°	48.3
45°	33.8
47.5°	22.9
50°	16.6
52.5°	14.0
55°	12.5
57.5°	10.9
60°	9.4
62.5°	8.3
65°	7.3
67.5°	6.2
70°	5.2
72.5°	4.2
75°	3.6
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)