

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259333

Luminaire Tested: P3AS05R509050DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259333
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509050DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 5000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 302.0 lumens
Efficiency: N/A
Efficacy: 41.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259333

CATALOG NUMBER: P3AS05R509050DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1259333

CATALOG NUMBER: P3AS05R509050DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96155
5°	94211
10°	88242
15°	79002
20°	66482
25°	50737
30°	32967
35°	19542
40°	11307
45°	5675
50°	2115
55°	1644
60°	1535
65°	1401
70°	1346
75°	1356
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5675 cd/sqm

TEST NUMBER: P1259333

CATALOG NUMBER: P3AS05R509050DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.8	13.2
10°-20°	96.2	31.9
20°-30°	94.4	31.3
30°-40°	47.6	15.7
40°-50°	15.0	5.0
50°-60°	3.9	1.3
60°-70°	2.7	0.9
70°-80°	1.7	0.6
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	230.5	76.3
0°-40°	278.0	92.1
0°-60°	297.0	98.3
0°-90°	302.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	302.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	438	
5°	428	40
15°	348	96
25°	210	94
35°	73	48
45°	18	15
55°	4	4
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1259333

CATALOG NUMBER: P3AS05R509050DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	438.5
2.5°	435.8
5°	428.0
7.5°	414.1
10°	396.3
12.5°	373.5
15°	348.0
17.5°	318.5
20°	284.9
22.5°	248.6
25°	209.7
27.5°	168.4
30°	130.2
32.5°	98.0
35°	73.0
37.5°	54.0
40°	39.5
42.5°	27.9
45°	18.3
47.5°	10.5
50°	6.2
52.5°	4.6
55°	4.3
57.5°	3.8
60°	3.5
62.5°	3.2
65°	2.7
67.5°	2.4
70°	2.1
72.5°	1.9
75°	1.6
77.5°	1.3
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)