

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259340

Luminaire Tested: P3AS05R509050DE010 E3DLD1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1259340  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R509050DE010 E3DLD1H  
Description: 3in Adjustable LED luminaire with, R50 optic, 5000K CCT AND, 90CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 479.1 lumens  
Efficiency: N/A  
Efficacy: 66.5 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1259340  
CATALOG NUMBER: P3AS05R509050DE010 E3DLD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1259340  
 CATALOG NUMBER: P3AS05R509050DE010 E3DLD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	97339
5°	95906
10°	91671
15°	84881
20°	76283
25°	67068
30°	57021
35°	46257
40°	34751
45°	22390
50°	10644
55°	8372
60°	7894
65°	7368
70°	6668
75°	6015
80°	5556
85°	5535

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22390 cd/sqm



TEST NUMBER: P1259340  
 CATALOG NUMBER: P3AS05R509050DE010 E3DLD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.8	8.5
10°-20°	104.3	21.8
20°-30°	126.7	26.4
30°-40°	107.4	22.4
40°-50°	55.8	11.7
50°-60°	20.2	4.2
60°-70°	13.9	2.9
70°-80°	7.6	1.6
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	271.8	56.7
0°-40°	379.2	79.2
0°-60°	455.2	95.0
0°-90°	479.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	479.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	444	
5°	436	41
15°	374	104
25°	277	127
35°	173	107
45°	72	56
55°	22	20
65°	14	14
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P1259340  
CATALOG NUMBER: P3AS05R509050DE010 E3DLD1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	443.9
2.5°	442.3
5°	435.7
7.5°	425.9
10°	411.7
12.5°	393.6
15°	373.9
17.5°	351.5
20°	326.9
22.5°	301.8
25°	277.2
27.5°	251.5
30°	225.2
32.5°	199.0
35°	172.8
37.5°	147.1
40°	121.4
42.5°	96.8
45°	72.2
47.5°	48.1
50°	31.2
52.5°	24.1
55°	21.9
57.5°	19.7
60°	18.0
62.5°	15.9
65°	14.2
67.5°	12.0
70°	10.4
72.5°	8.7
75°	7.1
77.5°	5.5
80°	4.4
82.5°	3.3
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)