

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260110

Luminaire Tested: P3AS13R559050DE010 E3D1LI

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1260110  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R559050DE010 E3D1LI  
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1370.0 lumens  
Efficiency: N/A  
Efficacy: 93.8 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260110  
CATALOG NUMBER: P3AS13R559050DE010 E3D1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1260110

CATALOG NUMBER: P3AS13R559050DE010 E3D1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79	79	79	79
5	95	88	83	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	83	75	69	66	82	74	69	66	73	69	65	72	68	65	71	68	65	63	63	63	63
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	57	57	57	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	397293
5°	383226
10°	396920
15°	391330
20°	362165
25°	292904
30°	175546
35°	59481
40°	16402
45°	7257
50°	2115
55°	382
60°	219
65°	259
70°	321
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7257 cd/sqm



TEST NUMBER: P1260110  
 CATALOG NUMBER: P3AS13R559050DE010 E3D1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.4	12.3
10°-20°	479.9	35.0
20°-30°	533.5	38.9
30°-40°	166.1	12.1
40°-50°	19.9	1.5
50°-60°	1.5	0.1
60°-70°	0.5	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1181.9	86.3
0°-40°	1347.9	98.4
0°-60°	1369.4	100.0
0°-90°	1370.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1370.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1812	
5°	1741	168
15°	1724	480
25°	1211	533
35°	222	166
45°	23	20
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1260110  
CATALOG NUMBER: P3AS13R559050DE010 E3D1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1811.8
1°	1805.0
2°	1787.3
3°	1765.4
4°	1745.7
5°	1741.0
6°	1746.2
7°	1757.1
8°	1769.6
9°	1779.5
10°	1782.6
11°	1780.5
12°	1772.2
13°	1759.2
14°	1744.1
15°	1723.8
16°	1700.4
17°	1670.7
18°	1637.4
19°	1597.3
20°	1552.0
21°	1500.5
22°	1439.6
23°	1372.5
24°	1295.5
25°	1210.6
26°	1117.5
27°	1018.6
28°	912.9
29°	804.1
30°	693.3
31°	581.9
32°	473.1
32.5°	424.7
33°	374.7
34°	289.9
35°	222.2
36°	169.2
37°	125.4
37.5°	107.2
38°	93.2
39°	70.8
40°	57.3
42.5°	36.4
45°	23.4



TEST NUMBER: P1260110  
CATALOG NUMBER: P3AS13R559050DE010 E3D1LI

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	14.1
50°	6.2
52.5°	2.1
55°	1.0
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)