

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260128

Luminaire Tested: P3AS13R559050DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559050DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 772.0 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260128

CATALOG NUMBER: P3AS13R559050DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1260128

CATALOG NUMBER: P3AS13R559050DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	210005
5°	204732
10°	190333
15°	169513
20°	144049
25°	116233
30°	88621
35°	63042
40°	41592
45°	24654
50°	14464
55°	8908
60°	7894
65°	7160
70°	6091
75°	5422
80°	5304
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24654 cd/sqm

TEST NUMBER: P1260128

CATALOG NUMBER: P3AS13R559050DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.4	11.2
10°-20°	207.0	26.8
20°-30°	219.2	28.4
30°-40°	148.2	19.2
40°-50°	64.9	8.4
50°-60°	23.2	3.0
60°-70°	13.6	1.8
70°-80°	7.1	0.9
80°-90°	2.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	512.6	66.4
0°-40°	660.7	85.6
0°-60°	748.9	97.0
0°-90°	772.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	772.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	958	
5°	930	86
15°	747	207
25°	480	219
35°	236	148
45°	80	65
55°	23	23
65°	14	14
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1260128

CATALOG NUMBER: P3AS13R559050DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	957.7
2.5°	950.3
5°	930.1
7.5°	897.3
10°	854.8
12.5°	803.9
15°	746.7
17.5°	683.0
20°	617.3
22.5°	548.3
25°	480.4
27.5°	413.6
30°	350.0
32.5°	289.5
35°	235.5
37.5°	186.7
40°	145.3
42.5°	109.2
45°	79.5
47.5°	58.3
50°	42.4
52.5°	29.7
55°	23.3
57.5°	21.2
60°	18.0
62.5°	15.9
65°	13.8
67.5°	11.7
70°	9.5
72.5°	8.5
75°	6.4
77.5°	5.3
80°	4.2
82.5°	3.2
85°	2.1
87.5°	1.1
90°	0.0

(END OF REPORT)