

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259362

Luminaire Tested: P3AS05R559050DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559050DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 292.0 lumens
Efficiency: N/A
Efficacy: 40.6 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259362

CATALOG NUMBER: P3AS05R559050DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1259362

CATALOG NUMBER: P3AS05R559050DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80191
5°	79375
10°	76641
15°	70852
20°	61139
25°	48293
30°	34258
35°	22085
40°	13253
45°	7474
50°	4025
55°	1453
60°	1272
65°	1245
70°	1218
75°	1101
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7474 cd/sqm

TEST NUMBER: P1259362

CATALOG NUMBER: P3AS05R559050DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.9	11.6
10°-20°	86.3	29.6
20°-30°	90.4	31.0
30°-40°	52.8	18.1
40°-50°	19.7	6.8
50°-60°	4.7	1.6
60°-70°	2.4	0.8
70°-80°	1.4	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	210.6	72.1
0°-40°	263.4	90.2
0°-60°	287.8	98.6
0°-90°	292.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	292.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	366	
5°	361	34
15°	312	86
25°	200	90
35°	82	53
45°	24	20
55°	4	5
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1259362

CATALOG NUMBER: P3AS05R559050DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	365.7
2.5°	364.6
5°	360.6
7.5°	354.1
10°	344.2
12.5°	330.3
15°	312.1
17.5°	289.0
20°	262.0
22.5°	231.7
25°	199.6
27.5°	166.6
30°	135.3
32.5°	106.9
35°	82.5
37.5°	62.7
40°	46.3
42.5°	33.2
45°	24.1
47.5°	17.4
50°	11.8
52.5°	6.7
55°	3.8
57.5°	3.2
60°	2.9
62.5°	2.7
65°	2.4
67.5°	2.1
70°	1.9
72.5°	1.6
75°	1.3
77.5°	1.1
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)