

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260130

Luminaire Tested: P3AS13R559050DE010 E3DLP1WH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1260130  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R559050DE010 E3DLP1WH  
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1157.0 lumens  
Efficiency: N/A  
Efficacy: 79.2 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260130

CATALOG NUMBER: P3AS13R559050DE010 E3DLP1WH

### Luminous Intensity Polar Plot



TEST NUMBER: P1260130

CATALOG NUMBER: P3AS13R559050DE010 E3DLP1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 |  | 101 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 94  | 98  | 95  | 92  |  | 95  | 92  | 90  |  | 92  |
| 3   | 102 | 96  | 91  | 87  | 100 | 94  | 90  | 86  | 92  | 88  | 85  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 90  | 84  | 80  | 95  | 89  | 83  | 79  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 82  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 78  | 74  | 81  | 77  | 73  |  | 80  | 76  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 73  | 68  | 77  | 72  | 68  |  | 75  | 71  | 68  |  | 74  |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  |  | 71  | 67  | 63  |  | 70  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 63  | 60  |  | 67  | 63  | 60  |  | 67  |
| 9   | 76  | 66  | 61  | 57  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 73  | 63  | 57  | 53  | 72  | 62  | 57  | 53  | 62  | 57  | 53  |  | 61  | 56  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 317694 |
| 5°  | 314483 |
| 10° | 303691 |
| 15° | 280728 |
| 20° | 242244 |
| 25° | 191334 |
| 30° | 135717 |
| 35° | 87509  |
| 40° | 52556  |
| 45° | 29615  |
| 50° | 15931  |
| 55° | 5696   |
| 60° | 5131   |
| 65° | 4981   |
| 70° | 4744   |
| 75° | 4490   |
| 80° | 4041   |
| 85° | 2768   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29615 cd/sqm

TEST NUMBER: P1260130

CATALOG NUMBER: P3AS13R559050DE010 E3DLP1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 134.4  | 11.6      |
| 10°-20°   | 341.9  | 29.6      |
| 20°-30°   | 358.3  | 31.0      |
| 30°-40°   | 209.1  | 18.1      |
| 40°-50°   | 78.2   | 6.8       |
| 50°-60°   | 18.4   | 1.6       |
| 60°-70°   | 9.5    | 0.8       |
| 70°-80°   | 5.6    | 0.5       |
| 80°-90°   | 1.6    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 834.7  | 72.1      |
| 0°-40°    | 1043.7 | 90.2      |
| 0°-60°    | 1140.3 | 98.6      |
| 0°-90°    | 1157.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1157.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1449 |      |
| 5°  | 1429 | 134  |
| 15° | 1237 | 342  |
| 25° | 791  | 358  |
| 35° | 327  | 209  |
| 45° | 96   | 78   |
| 55° | 15   | 18   |
| 65° | 10   | 9    |
| 75° | 5    | 6    |
| 85° | 1    | 2    |
| 90° | 0    |      |

TEST NUMBER: P1260130

CATALOG NUMBER: P3AS13R559050DE010 E3DLP1WH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1448.8 |
| 2.5°  | 1444.6 |
| 5°    | 1428.7 |
| 7.5°  | 1403.2 |
| 10°   | 1363.9 |
| 12.5° | 1308.7 |
| 15°   | 1236.6 |
| 17.5° | 1145.3 |
| 20°   | 1038.1 |
| 22.5° | 918.1  |
| 25°   | 790.8  |
| 27.5° | 660.2  |
| 30°   | 536.0  |
| 32.5° | 423.5  |
| 35°   | 326.9  |
| 37.5° | 248.4  |
| 40°   | 183.6  |
| 42.5° | 131.6  |
| 45°   | 95.5   |
| 47.5° | 69.0   |
| 50°   | 46.7   |
| 52.5° | 26.5   |
| 55°   | 14.9   |
| 57.5° | 12.7   |
| 60°   | 11.7   |
| 62.5° | 10.6   |
| 65°   | 9.6    |
| 67.5° | 8.5    |
| 70°   | 7.4    |
| 72.5° | 6.4    |
| 75°   | 5.3    |
| 77.5° | 4.2    |
| 80°   | 3.2    |
| 82.5° | 2.1    |
| 85°   | 1.1    |
| 87.5° | 1.1    |
| 90°   | 0.0    |

(END OF REPORT)