

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260155

Luminaire Tested: P3AS13R609050DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260155
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609050DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 5000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 378.0 lumens
Efficiency: N/A
Efficacy: 25.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260155

CATALOG NUMBER: P3AS13R609050DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1260155

CATALOG NUMBER: P3AS13R609050DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95804
5°	93638
10°	87685
15°	78661
20°	67649
25°	55939
30°	44184
35°	32819
40°	22614
45°	14172
50°	7812
55°	4549
60°	4122
65°	3528
70°	3013
75°	3050
80°	2652
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14172 cd/sqm

TEST NUMBER: P1260155

CATALOG NUMBER: P3AS13R609050DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.6	10.5
10°-20°	96.2	25.5
20°-30°	105.6	27.9
30°-40°	76.9	20.3
40°-50°	36.3	9.6
50°-60°	11.9	3.1
60°-70°	6.8	1.8
70°-80°	3.6	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	241.4	63.9
0°-40°	318.3	84.2
0°-60°	366.5	97.0
0°-90°	378.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	378.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	437	
5°	425	40
15°	346	96
25°	231	106
35°	123	77
45°	46	36
55°	12	12
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1260155

CATALOG NUMBER: P3AS13R609050DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	436.9
2.5°	434.3
5°	425.4
7.5°	411.9
10°	393.8
12.5°	371.9
15°	346.5
17.5°	319.0
20°	289.9
22.5°	260.3
25°	231.2
27.5°	202.1
30°	174.5
32.5°	148.0
35°	122.6
37.5°	99.7
40°	79.0
42.5°	60.8
45°	45.7
47.5°	33.2
50°	22.9
52.5°	15.1
55°	11.9
57.5°	10.4
60°	9.4
62.5°	7.8
65°	6.8
67.5°	5.7
70°	4.7
72.5°	4.2
75°	3.6
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)