

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259378

Luminaire Tested: P3AS05R559050DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559050DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 596.0 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259378

CATALOG NUMBER: P3AS05R559050DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1259378

CATALOG NUMBER: P3AS05R559050DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	95	90	86	92	88	85		89	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	163649
5°	161985
10°	156443
15°	144609
20°	124774
25°	98546
30°	69909
35°	45079
40°	27079
45°	15257
50°	8221
55°	2944
60°	2631
65°	2542
70°	2436
75°	2288
80°	2020
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15257 cd/sqm

TEST NUMBER: P1259378

CATALOG NUMBER: P3AS05R559050DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.2	11.6
10°-20°	176.1	29.6
20°-30°	184.6	31.0
30°-40°	107.7	18.1
40°-50°	40.3	6.8
50°-60°	9.5	1.6
60°-70°	4.9	0.8
70°-80°	2.9	0.5
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	430.0	72.1
0°-40°	537.6	90.2
0°-60°	587.4	98.6
0°-90°	596.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	596.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	746	
5°	736	69
15°	637	176
25°	407	185
35°	168	108
45°	49	40
55°	8	10
65°	5	5
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1259378

CATALOG NUMBER: P3AS05R559050DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	746.3
2.5°	744.1
5°	735.9
7.5°	722.8
10°	702.6
12.5°	674.2
15°	637.0
17.5°	590.0
20°	534.7
22.5°	473.0
25°	407.3
27.5°	340.1
30°	276.1
32.5°	218.2
35°	168.4
37.5°	127.9
40°	94.6
42.5°	67.8
45°	49.2
47.5°	35.5
50°	24.1
52.5°	13.7
55°	7.7
57.5°	6.6
60°	6.0
62.5°	5.5
65°	4.9
67.5°	4.4
70°	3.8
72.5°	3.3
75°	2.7
77.5°	2.2
80°	1.6
82.5°	1.1
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)