

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260172

Luminaire Tested: P3AS13R659050DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260172
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659050DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 522.0 lumens
Efficiency: N/A
Efficacy: 35.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260172
CATALOG NUMBER: P3AS13R659050DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1260172
 CATALOG NUMBER: P3AS13R659050DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63			63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123104
5°	121615
10°	117010
15°	109603
20°	98592
25°	83715
30°	65478
35°	46659
40°	30543
45°	18886
50°	9586
55°	3364
60°	2982
65°	2958
70°	2693
75°	2626
80°	2652
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18886 cd/sqm



TEST NUMBER: P1260172
 CATALOG NUMBER: P3AS13R659050DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.9	9.9
10°-20°	134.4	25.7
20°-30°	157.0	30.1
30°-40°	109.8	21.0
40°-50°	48.3	9.3
50°-60°	10.8	2.1
60°-70°	5.5	1.0
70°-80°	3.3	0.6
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	343.3	65.8
0°-40°	453.0	86.8
0°-60°	512.1	98.1
0°-90°	522.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	522.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	561	
5°	552	52
15°	483	134
25°	346	157
35°	174	110
45°	61	48
55°	9	11
65°	6	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1260172
CATALOG NUMBER: P3AS13R659050DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	561.4
2.5°	559.3
5°	552.5
7.5°	541.1
10°	525.5
12.5°	506.2
15°	482.8
17.5°	454.2
20°	422.5
22.5°	386.6
25°	346.0
27.5°	303.3
30°	258.6
32.5°	215.4
35°	174.3
37.5°	138.4
40°	106.7
42.5°	80.6
45°	60.9
47.5°	44.7
50°	28.1
52.5°	14.6
55°	8.8
57.5°	7.8
60°	6.8
62.5°	6.2
65°	5.7
67.5°	4.7
70°	4.2
72.5°	3.6
75°	3.1
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)