

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260187

Luminaire Tested: P3AS13R659050DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260187
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659050DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 5000K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 736.0 lumens
Efficiency: N/A
Efficacy: 50.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260187

CATALOG NUMBER: P3AS13R659050DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1260187

CATALOG NUMBER: P3AS13R659050DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	187068
5°	182412
10°	169892
15°	152237
20°	131495
25°	109361
30°	86241
35°	63925
40°	44054
45°	27321
50°	14840
55°	9328
60°	7894
65°	7160
70°	6155
75°	5422
80°	5304
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27321 cd/sqm

TEST NUMBER: P1260187

CATALOG NUMBER: P3AS13R659050DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	10.5
10°-20°	186.4	25.3
20°-30°	206.1	28.0
30°-40°	149.7	20.3
40°-50°	70.1	9.5
50°-60°	23.6	3.2
60°-70°	13.6	1.9
70°-80°	7.1	1.0
80°-90°	2.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	469.5	63.8
0°-40°	619.2	84.1
0°-60°	712.9	96.9
0°-90°	736.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	736.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	853	
5°	829	77
15°	671	186
25°	452	206
35°	239	150
45°	88	70
55°	24	24
65°	14	14
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1260187

CATALOG NUMBER: P3AS13R659050DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	853.1
2.5°	847.8
5°	828.7
7.5°	800.1
10°	763.0
12.5°	719.4
15°	670.6
17.5°	617.6
20°	563.5
22.5°	507.2
25°	452.0
27.5°	395.8
30°	340.6
32.5°	287.6
35°	238.8
37.5°	194.2
40°	153.9
42.5°	117.8
45°	88.1
47.5°	63.7
50°	43.5
52.5°	29.7
55°	24.4
57.5°	21.2
60°	18.0
62.5°	15.9
65°	13.8
67.5°	11.7
70°	9.6
72.5°	8.5
75°	6.4
77.5°	5.3
80°	4.2
82.5°	3.2
85°	2.1
87.5°	1.1
90°	0.0

(END OF REPORT)