

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260204

Luminaire Tested: P3AS13R709050DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260204
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709050DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R70 optic, 5000K CCT AND, 90CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1069.0 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260204
CATALOG NUMBER: P3AS13R709050DE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1260204
 CATALOG NUMBER: P3AS13R709050DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84			84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77			77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70			70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65			65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44			44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	206957
5°	204468
10°	198549
15°	190149
20°	178119
25°	161816
30°	139768
35°	111387
40°	81123
45°	53339
50°	25006
55°	7723
60°	7456
65°	7160
70°	6796
75°	7202
80°	6693
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 53339 cd/sqm



TEST NUMBER: P1260204
 CATALOG NUMBER: P3AS13R709050DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.5	8.2
10°-20°	234.4	21.9
20°-30°	304.7	28.5
30°-40°	258.5	24.2
40°-50°	133.3	12.5
50°-60°	25.7	2.4
60°-70°	13.9	1.3
70°-80°	8.6	0.8
80°-90°	2.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	626.6	58.6
0°-40°	885.1	82.8
0°-60°	1044.1	97.7
0°-90°	1069.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1069.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	944	
5°	929	87
15°	838	234
25°	669	305
35°	416	259
45°	172	133
55°	20	26
65°	14	14
75°	8	9
85°	2	2
90°	0	



TEST NUMBER: P1260204
CATALOG NUMBER: P3AS13R709050DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	943.8
2.5°	940.6
5°	928.9
7.5°	911.9
10°	891.7
12.5°	866.3
15°	837.6
17.5°	802.6
20°	763.3
22.5°	718.7
25°	668.8
27.5°	612.5
30°	552.0
32.5°	485.2
35°	416.1
37.5°	348.2
40°	283.4
42.5°	222.9
45°	172.0
47.5°	126.3
50°	73.3
52.5°	31.8
55°	20.2
57.5°	19.1
60°	17.0
62.5°	15.9
65°	13.8
67.5°	12.7
70°	10.6
72.5°	9.6
75°	8.5
77.5°	6.4
80°	5.3
82.5°	3.2
85°	2.1
87.5°	1.1
90°	0.0

(END OF REPORT)