

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259458

Luminaire Tested: P3AS05R709050DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259458
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709050DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R70 optic, 5000K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 393.0 lumens
Efficiency: N/A
Efficacy: 54.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259458

CATALOG NUMBER: P3AS05R709050DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1259458

CATALOG NUMBER: P3AS05R709050DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102			100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94			92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86			84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79			77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73			71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67			65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62			61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54			52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50			49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92186
5°	90491
10°	85325
15°	77435
20°	67743
25°	57148
30°	46792
35°	36299
40°	25963
45°	16436
50°	8221
55°	5008
60°	4298
65°	3995
70°	3526
75°	3219
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16436 cd/sqm

TEST NUMBER: P1259458

CATALOG NUMBER: P3AS05R709050DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.4	9.8
10°-20°	94.9	24.2
20°-30°	108.1	27.5
30°-40°	84.5	21.5
40°-50°	41.5	10.6
50°-60°	12.8	3.3
60°-70°	7.6	1.9
70°-80°	4.0	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	241.4	61.4
0°-40°	325.9	82.9
0°-60°	380.2	96.7
0°-90°	393.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	393.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	420	
5°	411	38
15°	341	95
25°	236	108
35°	136	85
45°	53	42
55°	13	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1259458

CATALOG NUMBER: P3AS05R709050DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	420.4
2.5°	418.2
5°	411.1
7.5°	399.6
10°	383.2
12.5°	364.1
15°	341.1
17.5°	316.5
20°	290.3
22.5°	262.9
25°	236.2
27.5°	209.9
30°	184.8
32.5°	159.6
35°	135.6
37.5°	112.6
40°	90.7
42.5°	70.5
45°	53.0
47.5°	37.2
50°	24.1
52.5°	15.9
55°	13.1
57.5°	11.5
60°	9.8
62.5°	8.7
65°	7.7
67.5°	6.6
70°	5.5
72.5°	4.4
75°	3.8
77.5°	3.3
80°	2.2
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)