

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260209

Luminaire Tested: P3AS13R709050DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260209
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709050DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 5000K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 763.0 lumens
Efficiency: N/A
Efficacy: 52.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260209

CATALOG NUMBER: P3AS13R709050DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1260209

CATALOG NUMBER: P3AS13R709050DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	88	83		98	92	87	83		89	85	81		87	83	80		84	81	79
4	95	86	80	76		93	85	80	75		83	78	74		81	77	73		79	76	73
5	89	80	74	69		88	79	73	69		78	72	68		76	71	68		74	70	67
6	85	75	68	64		83	74	68	64		73	67	63		71	66	63		70	65	62
7	80	70	64	59		79	69	63	59		68	62	58		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	62	55	51		71	61	55	51		60	55	51		59	54	51		58	54	50
10	69	58	52	48		67	58	52	48		57	51	48		56	51	48		55	51	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	178977
5°	175676
10°	165662
15°	150353
20°	131518
25°	110934
30°	90824
35°	70457
40°	50437
45°	31910
50°	15931
55°	9749
60°	8377
65°	7731
70°	6796
75°	6270
80°	5304
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 31910 cd/sqm

TEST NUMBER: P1260209

CATALOG NUMBER: P3AS13R709050DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.5	9.8
10°-20°	184.3	24.2
20°-30°	209.9	27.5
30°-40°	164.1	21.5
40°-50°	80.6	10.6
50°-60°	24.8	3.3
60°-70°	14.7	1.9
70°-80°	7.8	1.0
80°-90°	2.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	468.6	61.4
0°-40°	632.7	82.9
0°-60°	738.2	96.7
0°-90°	763.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	763.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	816	
5°	798	74
15°	662	184
25°	458	210
35°	263	164
45°	103	81
55°	26	25
65°	15	15
75°	7	8
85°	2	2
90°	0	

TEST NUMBER: P1260209

CATALOG NUMBER: P3AS13R709050DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	816.2
2.5°	811.9
5°	798.1
7.5°	775.8
10°	744.0
12.5°	706.9
15°	662.3
17.5°	614.5
20°	563.6
22.5°	510.5
25°	458.5
27.5°	407.6
30°	358.7
32.5°	309.9
35°	263.2
37.5°	218.6
40°	176.2
42.5°	136.9
45°	102.9
47.5°	72.2
50°	46.7
52.5°	30.8
55°	25.5
57.5°	22.3
60°	19.1
62.5°	17.0
65°	14.9
67.5°	12.7
70°	10.6
72.5°	8.5
75°	7.4
77.5°	6.4
80°	4.2
82.5°	3.2
85°	2.1
87.5°	1.1
90°	0.0

(END OF REPORT)