

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260268

Luminaire Tested: P3AS17R159050DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260268
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159050DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 5000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1110.0 lumens
Efficiency: N/A
Efficacy: 52.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260268

CATALOG NUMBER: P3AS17R159050DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1260268

CATALOG NUMBER: P3AS17R159050DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	279978
5°	272396
10°	248915
15°	218026
20°	187033
25°	156154
30°	124981
35°	93719
40°	68013
45°	44470
50°	27837
55°	18809
60°	16665
65°	15306
70°	14426
75°	13132
80°	12375
85°	10567

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 44470 cd/sqm

TEST NUMBER: P1260268

CATALOG NUMBER: P3AS17R159050DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.2	10.3
10°-20°	267.6	24.1
20°-30°	294.8	26.6
30°-40°	220.8	19.9
40°-50°	114.4	10.3
50°-60°	47.5	4.3
60°-70°	29.4	2.6
70°-80°	16.5	1.5
80°-90°	4.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	676.6	61.0
0°-40°	897.4	80.9
0°-60°	1059.3	95.4
0°-90°	1110.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1110.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1277	
5°	1238	114
15°	960	268
25°	645	295
35°	350	221
45°	143	114
55°	49	47
65°	30	29
75°	16	17
85°	4	5
90°	0	

TEST NUMBER: P1260268

CATALOG NUMBER: P3AS17R159050DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1276.8
1°	1278.2
2°	1274.0
3°	1265.6
4°	1252.9
5°	1237.5
6°	1217.8
7°	1196.7
8°	1171.4
9°	1144.6
10°	1117.9
12.5°	1040.6
15°	960.4
17.5°	880.3
20°	801.5
22.5°	721.4
25°	645.4
27.5°	569.5
30°	493.6
32.5°	419.0
35°	350.1
37.5°	291.1
40°	237.6
42.5°	188.4
45°	143.4
47.5°	108.3
50°	81.6
52.5°	60.5
55°	49.2
57.5°	43.6
60°	38.0
62.5°	33.7
65°	29.5
67.5°	25.3
70°	22.5
72.5°	18.3
75°	15.5
77.5°	12.7
80°	9.8
82.5°	7.0
85°	4.2
87.5°	1.4
90°	0.0

(END OF REPORT)