

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260274

Luminaire Tested: P3AS17R159050DE010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1260274  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R159050DE010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R15 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 866.0 lumens  
Efficiency: N/A  
Efficacy: 40.8 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260274  
CATALOG NUMBER: P3AS17R159050DE010 E3DLP1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1260274  
 CATALOG NUMBER: P3AS17R159050DE010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	95	95	95	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	92	90	88	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	87	84	82	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	82	79	77	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	78	75	72	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	74	71	68	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	71	67	64	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	67	63	60	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	64	60	57	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	62	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	373435
5°	345145
10°	275546
15°	208151
20°	158494
25°	120781
30°	86520
35°	56456
40°	34608
45°	20932
50°	13919
55°	10743
60°	9254
65°	8042
70°	7245
75°	7117
80°	5304
85°	3522

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 20932 cd/sqm



TEST NUMBER: P1260274  
 CATALOG NUMBER: P3AS17R159050DE010 E3DLP1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.9	16.0
10°-20°	256.3	29.6
20°-30°	228.2	26.3
30°-40°	135.0	15.6
40°-50°	55.4	6.4
50°-60°	26.0	3.0
60°-70°	15.8	1.8
70°-80°	8.3	1.0
80°-90°	2.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	623.3	72.0
0°-40°	758.3	87.6
0°-60°	839.7	97.0
0°-90°	866.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	866.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1703	
5°	1568	139
15°	917	256
25°	499	228
35°	211	135
45°	68	55
55°	28	26
65°	16	16
75°	8	8
85°	1	2
90°	0	



TEST NUMBER: P1260274  
CATALOG NUMBER: P3AS17R159050DE010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1703.0
1°	1698.8
2°	1686.1
3°	1660.8
4°	1618.6
5°	1568.0
6°	1513.2
7°	1448.5
8°	1381.0
9°	1312.1
10°	1237.5
12.5°	1067.4
15°	916.9
17.5°	787.5
20°	679.2
22.5°	583.6
25°	499.2
27.5°	417.7
30°	341.7
32.5°	272.8
35°	210.9
37.5°	161.7
40°	120.9
42.5°	90.0
45°	67.5
47.5°	52.0
50°	40.8
52.5°	33.8
55°	28.1
57.5°	23.9
60°	21.1
62.5°	18.3
65°	15.5
67.5°	14.1
70°	11.3
72.5°	9.8
75°	8.4
77.5°	5.6
80°	4.2
82.5°	2.8
85°	1.4
87.5°	1.4
90°	0.0

(END OF REPORT)