

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260282

Luminaire Tested: P3AS17R209050DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260282
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209050DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R20 optic, 5000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1776.0 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260282
CATALOG NUMBER: P3AS17R209050DE010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1260282
 CATALOG NUMBER: P3AS17R209050DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	98	98	98
2	112	109	107	104	110	108	105	103	104	103	101	102	100	99	99	98	97	97	97	97	95
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	95	95	95	93
4	107	102	99	96	105	101	98	96	99	97	95	97	95	93	96	94	92	92	92	92	91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	91	91	91	90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	89	89	89	88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	87	87	87	86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	85	85	85	85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	84	84	84	83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	87	84	82	82	82	82	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2758332
5°	2394139
10°	1479331
15°	513805
20°	157794
25°	55769
30°	20636
35°	8272
40°	4437
45°	1737
50°	955
55°	1070
60°	1228
65°	726
70°	898
75°	1186
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1737 cd/sqm



TEST NUMBER: P1260282
 CATALOG NUMBER: P3AS17R209050DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	902.7	50.8
10°-20°	716.2	40.3
20°-30°	124.0	7.0
30°-40°	22.5	1.3
40°-50°	5.2	0.3
50°-60°	2.5	0.1
60°-70°	1.6	0.1
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1742.9	98.1
0°-40°	1765.4	99.4
0°-60°	1773.1	99.8
0°-90°	1776.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1776.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12579	
5°	10877	903
15°	2263	716
25°	230	124
35°	31	23
45°	6	5
55°	3	3
65°	1	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1260282
CATALOG NUMBER: P3AS17R209050DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	12579.0
1°	12518.5
2°	12279.6
3°	11895.8
4°	11445.9
5°	10876.6
6°	10224.3
7°	9465.2
8°	8600.6
9°	7629.2
10°	6643.8
12.5°	4190.7
15°	2263.3
17.5°	1209.0
20°	676.2
22.5°	386.6
25°	230.5
27.5°	140.6
30°	81.5
32.5°	47.8
35°	30.9
37.5°	21.1
40°	15.5
42.5°	9.8
45°	5.6
47.5°	2.8
50°	2.8
52.5°	2.8
55°	2.8
57.5°	2.8
60°	2.8
62.5°	1.4
65°	1.4
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	1.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)