

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260297

Luminaire Tested: P3AS17R209050DE010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1260297  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R209050DE010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R20 optic, 5000K CCT AND, 90CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1107.0 lumens  
Efficiency: N/A  
Efficacy: 52.2 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1260297

CATALOG NUMBER: P3AS17R209050DE010 E3DLD1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1260297

CATALOG NUMBER: P3AS17R209050DE010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 113 | 109 | 106 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 95  | 93  | 91  |    |    |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 94  | 91  | 95  | 92  | 89  | 92  | 89  | 87  | 90  | 87  | 85  | 83  |    |    |
| 3   | 100 | 93  | 87  | 82  | 98  | 91  | 86  | 82  | 88  | 84  | 80  | 86  | 82  | 79  | 84  | 81  | 78  | 76  |    |    |
| 4   | 94  | 86  | 79  | 75  | 92  | 85  | 79  | 74  | 82  | 77  | 73  | 80  | 76  | 72  | 78  | 75  | 72  | 70  |    |    |
| 5   | 89  | 80  | 73  | 68  | 87  | 79  | 73  | 68  | 77  | 71  | 67  | 75  | 70  | 67  | 73  | 69  | 66  | 65  |    |    |
| 6   | 84  | 74  | 68  | 63  | 82  | 73  | 67  | 63  | 72  | 66  | 62  | 70  | 65  | 62  | 69  | 65  | 61  | 60  |    |    |
| 7   | 80  | 69  | 63  | 58  | 78  | 69  | 62  | 58  | 67  | 62  | 58  | 66  | 61  | 57  | 65  | 60  | 57  | 55  |    |    |
| 8   | 75  | 65  | 59  | 54  | 74  | 64  | 58  | 54  | 63  | 58  | 54  | 62  | 57  | 53  | 61  | 57  | 53  | 52  |    |    |
| 9   | 72  | 61  | 55  | 50  | 70  | 61  | 55  | 50  | 60  | 54  | 50  | 59  | 54  | 50  | 58  | 53  | 50  | 48  |    |    |
| 10  | 68  | 58  | 51  | 47  | 67  | 57  | 51  | 47  | 56  | 51  | 47  | 56  | 51  | 47  | 55  | 50  | 47  | 45  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 273816 |
| 5°  | 266497 |
| 10° | 245175 |
| 15° | 215801 |
| 20° | 185073 |
| 25° | 155477 |
| 30° | 125690 |
| 35° | 95620  |
| 40° | 68013  |
| 45° | 44904  |
| 50° | 27837  |
| 55° | 18274  |
| 60° | 16665  |
| 65° | 15306  |
| 70° | 14426  |
| 75° | 13132  |
| 80° | 12375  |
| 85° | 10567  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 44904 cd/sqm

TEST NUMBER: P1260297

CATALOG NUMBER: P3AS17R209050DE010 E3DLD1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 112.0  | 10.1      |
| 10°-20°   | 264.6  | 23.9      |
| 20°-30°   | 293.7  | 26.5      |
| 30°-40°   | 224.1  | 20.2      |
| 40°-50°   | 114.7  | 10.4      |
| 50°-60°   | 47.1   | 4.3       |
| 60°-70°   | 29.4   | 2.7       |
| 70°-80°   | 16.5   | 1.5       |
| 80°-90°   | 4.8    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 670.4  | 60.6      |
| 0°-40°    | 894.5  | 80.8      |
| 0°-60°    | 1056.3 | 95.4      |
| 0°-90°    | 1107.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1107.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1249 |      |
| 5°  | 1211 | 112  |
| 15° | 951  | 265  |
| 25° | 643  | 294  |
| 35° | 357  | 224  |
| 45° | 145  | 115  |
| 55° | 48   | 47   |
| 65° | 30   | 29   |
| 75° | 16   | 17   |
| 85° | 4    | 5    |
| 90° | 0    |      |

TEST NUMBER: P1260297

CATALOG NUMBER: P3AS17R209050DE010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1248.7 |
| 1°    | 1250.1 |
| 2°    | 1244.5 |
| 3°    | 1237.5 |
| 4°    | 1226.2 |
| 5°    | 1210.7 |
| 6°    | 1192.5 |
| 7°    | 1172.8 |
| 8°    | 1151.7 |
| 9°    | 1126.4 |
| 10°   | 1101.1 |
| 12.5° | 1027.9 |
| 15°   | 950.6  |
| 17.5° | 871.8  |
| 20°   | 793.1  |
| 22.5° | 714.3  |
| 25°   | 642.6  |
| 27.5° | 570.9  |
| 30°   | 496.4  |
| 32.5° | 426.1  |
| 35°   | 357.2  |
| 37.5° | 296.7  |
| 40°   | 237.6  |
| 42.5° | 187.0  |
| 45°   | 144.8  |
| 47.5° | 109.7  |
| 50°   | 81.6   |
| 52.5° | 60.5   |
| 55°   | 47.8   |
| 57.5° | 43.6   |
| 60°   | 38.0   |
| 62.5° | 33.7   |
| 65°   | 29.5   |
| 67.5° | 25.3   |
| 70°   | 22.5   |
| 72.5° | 18.3   |
| 75°   | 15.5   |
| 77.5° | 12.7   |
| 80°   | 9.8    |
| 82.5° | 7.0    |
| 85°   | 4.2    |
| 87.5° | 1.4    |
| 90°   | 0.0    |

(END OF REPORT)