

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259629

Luminaire Tested: P3AS09R409050DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409050DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 5000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 931.0 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259629

CATALOG NUMBER: P3AS09R409050DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1259629

CATALOG NUMBER: P3AS09R409050DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	411963
5°	399999
10°	362986
15°	299866
20°	216319
25°	133798
30°	72442
35°	37423
40°	20352
45°	11412
50°	5731
55°	4282
60°	3859
65°	3736
70°	3590
75°	3389
80°	3031
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11412 cd/sqm

TEST NUMBER: P1259629

CATALOG NUMBER: P3AS09R409050DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.5	18.0
10°-20°	359.7	38.6
20°-30°	256.7	27.6
30°-40°	94.5	10.1
40°-50°	29.8	3.2
50°-60°	10.4	1.1
60°-70°	7.1	0.8
70°-80°	4.2	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	783.9	84.2
0°-40°	878.4	94.3
0°-60°	918.5	98.7
0°-90°	931.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	931.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1879	
5°	1817	168
15°	1321	360
25°	553	257
35°	140	94
45°	37	30
55°	11	10
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1259629

CATALOG NUMBER: P3AS09R409050DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1878.7
2.5°	1864.3
5°	1817.2
7.5°	1738.8
10°	1630.2
12.5°	1491.9
15°	1320.9
17.5°	1129.1
20°	927.0
22.5°	728.0
25°	553.0
27.5°	405.9
30°	286.1
32.5°	200.6
35°	139.8
37.5°	99.1
40°	71.1
42.5°	51.1
45°	36.8
47.5°	24.8
50°	16.8
52.5°	12.0
55°	11.2
57.5°	10.4
60°	8.8
62.5°	8.0
65°	7.2
67.5°	6.4
70°	5.6
72.5°	4.8
75°	4.0
77.5°	3.2
80°	2.4
82.5°	1.6
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)