

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259724

Luminaire Tested: P3AS09R559050DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259724
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559050DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 582.0 lumens
Efficiency: N/A
Efficacy: 52.4 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259724

CATALOG NUMBER: P3AS09R559050DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1259724

CATALOG NUMBER: P3AS09R559050DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158321
5°	154347
10°	143484
15°	127787
20°	108579
25°	87634
30°	66820
35°	47515
40°	31344
45°	18607
50°	10916
55°	6729
60°	5964
65°	5396
70°	4616
75°	4067
80°	4041
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18607 cd/sqm

TEST NUMBER: P1259724

CATALOG NUMBER: P3AS09R559050DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.1	11.2
10°-20°	156.0	26.8
20°-30°	165.3	28.4
30°-40°	111.7	19.2
40°-50°	49.0	8.4
50°-60°	17.5	3.0
60°-70°	10.3	1.8
70°-80°	5.4	0.9
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	386.4	66.4
0°-40°	498.1	85.6
0°-60°	564.6	97.0
0°-90°	582.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	582.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	722	
5°	701	65
15°	563	156
25°	362	165
35°	178	112
45°	60	49
55°	18	18
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1259724

CATALOG NUMBER: P3AS09R559050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	722.0
2.5°	716.4
5°	701.2
7.5°	676.4
10°	644.4
12.5°	606.1
15°	562.9
17.5°	514.9
20°	465.3
22.5°	413.4
25°	362.2
27.5°	311.8
30°	263.9
32.5°	218.3
35°	177.5
37.5°	140.7
40°	109.5
42.5°	82.4
45°	60.0
47.5°	44.0
50°	32.0
52.5°	22.4
55°	17.6
57.5°	16.0
60°	13.6
62.5°	12.0
65°	10.4
67.5°	8.8
70°	7.2
72.5°	6.4
75°	4.8
77.5°	4.0
80°	3.2
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)