

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260392

Luminaire Tested: P3AS17R359050DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R359050DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 5000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 912.0 lumens
Efficiency: N/A
Efficacy: 43.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260392
CATALOG NUMBER: P3AS17R359050DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1260392
 CATALOG NUMBER: P3AS17R359050DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 96 | 95 | 93 | | | |
| 2 | 107 | 102 | 98 | 94 | 105 | 100 | 97 | 93 | 97 | 94 | 91 | 94 | 92 | 89 | 91 | 89 | 87 | 86 | | | |
| 3 | 102 | 95 | 90 | 86 | 100 | 94 | 89 | 85 | 91 | 87 | 84 | 89 | 85 | 82 | 86 | 84 | 81 | 80 | | | |
| 4 | 97 | 89 | 83 | 79 | 95 | 88 | 82 | 78 | 86 | 81 | 77 | 84 | 80 | 77 | 82 | 78 | 76 | 74 | | | |
| 5 | 92 | 83 | 77 | 73 | 90 | 82 | 77 | 73 | 81 | 76 | 72 | 79 | 75 | 71 | 77 | 74 | 71 | 69 | | | |
| 6 | 87 | 78 | 72 | 68 | 86 | 77 | 72 | 68 | 76 | 71 | 67 | 75 | 70 | 67 | 73 | 69 | 66 | 65 | | | |
| 7 | 83 | 74 | 68 | 63 | 82 | 73 | 67 | 63 | 72 | 67 | 63 | 71 | 66 | 63 | 69 | 65 | 62 | 61 | | | |
| 8 | 79 | 70 | 64 | 60 | 78 | 69 | 63 | 59 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 59 | 57 | | | |
| 9 | 76 | 66 | 60 | 56 | 75 | 66 | 60 | 56 | 65 | 59 | 56 | 64 | 59 | 56 | 63 | 59 | 56 | 54 | | | |
| 10 | 72 | 63 | 57 | 53 | 71 | 62 | 57 | 53 | 61 | 56 | 53 | 61 | 56 | 53 | 60 | 56 | 53 | 51 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 293134 |
| 5° | 285912 |
| 10° | 261385 |
| 15° | 221863 |
| 20° | 175645 |
| 25° | 132854 |
| 30° | 96724 |
| 35° | 65397 |
| 40° | 40190 |
| 45° | 23072 |
| 50° | 13884 |
| 55° | 11278 |
| 60° | 9868 |
| 65° | 8769 |
| 70° | 7181 |
| 75° | 7117 |
| 80° | 7072 |
| 85° | 7045 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23072 cd/sqm

TEST NUMBER: P1260392

CATALOG NUMBER: P3AS17R359050DE010 E3DLP1WMH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 120.0 | 13.2 |
| 10°-20° | 269.4 | 29.5 |
| 20°-30° | 252.1 | 27.6 |
| 30°-40° | 154.3 | 16.9 |
| 40°-50° | 60.8 | 6.7 |
| 50°-60° | 26.8 | 2.9 |
| 60°-70° | 16.7 | 1.8 |
| 70°-80° | 8.9 | 1.0 |
| 80°-90° | 3.0 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 641.5 | 70.3 |
| 0°-40° | 795.8 | 87.3 |
| 0°-60° | 883.4 | 96.9 |
| 0°-90° | 912.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 912.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1337 | |
| 5° | 1299 | 120 |
| 15° | 977 | 269 |
| 25° | 549 | 252 |
| 35° | 244 | 154 |
| 45° | 74 | 61 |
| 55° | 30 | 27 |
| 65° | 17 | 17 |
| 75° | 8 | 9 |
| 85° | 3 | 3 |
| 90° | 0 | |

TEST NUMBER: P1260392

CATALOG NUMBER: P3AS17R359050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1336.8 |
| 1° | 1338.2 |
| 2° | 1334.0 |
| 3° | 1325.6 |
| 4° | 1313.0 |
| 5° | 1298.9 |
| 6° | 1280.7 |
| 7° | 1259.6 |
| 8° | 1234.3 |
| 9° | 1206.2 |
| 10° | 1173.9 |
| 11° | 1140.2 |
| 12° | 1103.7 |
| 13° | 1064.4 |
| 14° | 1020.9 |
| 15° | 977.3 |
| 17.5° | 865.0 |
| 20° | 752.7 |
| 22.5° | 644.5 |
| 25° | 549.1 |
| 27.5° | 460.6 |
| 30° | 382.0 |
| 32.5° | 308.9 |
| 35° | 244.3 |
| 37.5° | 186.8 |
| 40° | 140.4 |
| 42.5° | 101.1 |
| 45° | 74.4 |
| 47.5° | 53.4 |
| 50° | 40.7 |
| 52.5° | 33.7 |
| 55° | 29.5 |
| 57.5° | 25.3 |
| 60° | 22.5 |
| 62.5° | 19.7 |
| 65° | 16.9 |
| 67.5° | 14.0 |
| 70° | 11.2 |
| 72.5° | 9.8 |
| 75° | 8.4 |
| 77.5° | 7.0 |
| 80° | 5.6 |
| 82.5° | 4.2 |
| 85° | 2.8 |
| 87.5° | 1.4 |



TEST NUMBER: P1260392
CATALOG NUMBER: P3AS17R359050DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)