

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1259833

Luminaire Tested: P3AS10R129050DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1259833
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS10R129050DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R12 optic, 5000K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 457.0 lumens
Efficiency: N/A
Efficacy: 39.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1259833
CATALOG NUMBER: P3AS10R129050DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1259833
 CATALOG NUMBER: P3AS10R129050DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	197068
5°	182148
10°	145421
15°	109853
20°	83634
25°	63754
30°	45653
35°	29794
40°	18263
45°	11040
50°	7335
55°	5658
60°	4868
65°	4255
70°	3783
75°	3813
80°	2778
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11040 cd/sqm



TEST NUMBER: P1259833
 CATALOG NUMBER: P3AS10R129050DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.3	16.0
10°-20°	135.2	29.6
20°-30°	120.4	26.3
30°-40°	71.2	15.6
40°-50°	29.2	6.4
50°-60°	13.7	3.0
60°-70°	8.3	1.8
70°-80°	4.4	1.0
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	329.0	72.0
0°-40°	400.2	87.6
0°-60°	443.1	97.0
0°-90°	457.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	457.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	899	
5°	828	73
15°	484	135
25°	264	120
35°	111	71
45°	36	29
55°	15	14
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1259833
CATALOG NUMBER: P3AS10R129050DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	898.7
1°	896.5
2°	889.8
3°	876.4
4°	854.2
5°	827.5
6°	798.5
7°	764.4
8°	728.8
9°	692.4
10°	653.1
12.5°	563.3
15°	483.9
17.5°	415.6
20°	358.4
22.5°	308.0
25°	263.5
27.5°	220.4
30°	180.3
32.5°	144.0
35°	111.3
37.5°	85.3
40°	63.8
42.5°	47.5
45°	35.6
47.5°	27.5
50°	21.5
52.5°	17.8
55°	14.8
57.5°	12.6
60°	11.1
62.5°	9.6
65°	8.2
67.5°	7.4
70°	5.9
72.5°	5.2
75°	4.5
77.5°	3.0
80°	2.2
82.5°	1.5
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)