

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260412

Luminaire Tested: P3AS17R409050DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260412
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409050DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 5000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1638.0 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260412
CATALOG NUMBER: P3AS17R409050DE010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1260412
 CATALOG NUMBER: P3AS17R409050DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94	94	94	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84	84	84	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80	80	80	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	76	76	76	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72	72	72	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	65	65	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	63	63	63	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	60	60	60	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	724810
5°	703740
10°	638621
15°	527585
20°	380576
25°	235393
30°	127437
35°	65852
40°	35810
45°	20064
50°	10064
55°	7531
60°	6798
65°	6590
70°	6283
75°	5931
80°	5304
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20064 cd/sqm



TEST NUMBER: P1260412
 CATALOG NUMBER: P3AS17R409050DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.7	18.0
10°-20°	632.8	38.6
20°-30°	451.6	27.6
30°-40°	166.2	10.1
40°-50°	52.4	3.2
50°-60°	18.2	1.1
60°-70°	12.5	0.8
70°-80°	7.4	0.5
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1379.1	84.2
0°-40°	1545.4	94.3
0°-60°	1616.0	98.7
0°-90°	1638.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1638.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3305	
5°	3197	295
15°	2324	633
25°	973	452
35°	246	166
45°	65	52
55°	20	18
65°	13	13
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P1260412
CATALOG NUMBER: P3AS17R409050DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3305.4
2.5°	3280.1
5°	3197.1
7.5°	3059.3
10°	2868.1
12.5°	2624.9
15°	2324.0
17.5°	1986.6
20°	1630.9
22.5°	1280.8
25°	972.9
27.5°	714.2
30°	503.3
32.5°	352.9
35°	246.0
37.5°	174.3
40°	125.1
42.5°	90.0
45°	64.7
47.5°	43.6
50°	29.5
52.5°	21.1
55°	19.7
57.5°	18.3
60°	15.5
62.5°	14.1
65°	12.7
67.5°	11.2
70°	9.8
72.5°	8.4
75°	7.0
77.5°	5.6
80°	4.2
82.5°	2.8
85°	1.4
87.5°	1.4
90°	0.0

(END OF REPORT)