

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1260438

Luminaire Tested: P3AS17R459050DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1260438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459050DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 5000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 598.0 lumens
Efficiency: N/A
Efficacy: 28.2 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1260438
CATALOG NUMBER: P3AS17R459050DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1260438
 CATALOG NUMBER: P3AS17R459050DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	126788
5°	124543
10°	117856
15°	107492
20°	95045
25°	82529
30°	70846
35°	59026
40°	43997
45°	26918
50°	12452
55°	9749
60°	9385
65°	8561
70°	7950
75°	7625
80°	6945
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26918 cd/sqm



TEST NUMBER: P1260438
 CATALOG NUMBER: P3AS17R459050DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.9	8.8
10°-20°	131.8	22.0
20°-30°	156.6	26.2
30°-40°	136.1	22.8
40°-50°	68.2	11.4
50°-60°	23.7	4.0
60°-70°	16.6	2.8
70°-80°	9.3	1.6
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	341.3	57.1
0°-40°	477.4	79.8
0°-60°	569.3	95.2
0°-90°	598.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	598.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	578	
5°	566	53
15°	474	132
25°	341	157
35°	220	136
45°	87	68
55°	26	24
65°	16	17
75°	9	9
85°	2	3
90°	0	



TEST NUMBER: P1260438
CATALOG NUMBER: P3AS17R459050DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	578.2
2.5°	575.4
5°	565.8
7.5°	550.6
10°	529.3
12.5°	503.1
15°	473.5
17.5°	440.4
20°	407.3
22.5°	373.5
25°	341.1
27.5°	310.1
30°	279.8
32.5°	250.9
35°	220.5
37.5°	188.1
40°	153.7
42.5°	119.9
45°	86.8
47.5°	57.2
50°	36.5
52.5°	28.3
55°	25.5
57.5°	23.4
60°	21.4
62.5°	19.3
65°	16.5
67.5°	14.5
70°	12.4
72.5°	10.3
75°	9.0
77.5°	6.9
80°	5.5
82.5°	4.1
85°	2.1
87.5°	1.4
90°	0.0

(END OF REPORT)